



UPHOLSTERED CHAIRS



6000/9000 Series

INTEGRA SERIES



FEATURED MODEL

9551M-S-BKF-
3850S/5-AA

DIMENSIONS

SEAT

20" W x 18" D
3" Thick

MEDIUM BACK

17 1/2" W x 16" H
3" Thick

LARGE BACK

17 1/2" W x 19" H
3" Thick

UPHOLSTERY OPTIONS

STANDARD



BLACK



GRAY



BLACK VINYL



NAVY BLUE



ROYAL BLUE



BLUE VINYL

ESD



EBONY



NAVY BLUE



BLACK VINYL



GRAY



BLUE VINYL

CR & ESD/CR



BLACK VINYL



BLUE VINYL

BUILT TO ORDER

Each chair is configured to your exact specifications – choice of upholstery, arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Back Size	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model #	ESD Model #	Cleanroom ISO 4 Model #	Cleanroom ISO 5 Model #	Cleanroom ISO 6 Model #	Cleanroom ISO 7 Model #	ESD/CR ISO 4 Model #	ESD/CR ISO 5 Model #	ESD/CR ISO 6 Model #	ESD/CR ISO 7 Model #
DESK	25" Black Nylon	Medium	17" – 22"	Non Tilt	-	6000M	-	-	-	-	-	-	-	-	-
				Tilt	-	6001M	-	-	-	-	-	-	-	-	-
				Dlx Tilt	-	6002M	-	-	-	-	-	-	-	-	-
		Large	17" – 22"	Non Tilt	-	6000	-	-	-	-	-	-	-	-	-
				Tilt	-	6001	-	-	-	-	-	-	-	-	-
				Dlx Tilt	-	6002	-	-	-	-	-	-	-	-	-
	25" Polished Aluminum	Medium	15 ½" – 21"	Non Tilt	-	9050M-S	9050M-E	9050M-C1	9050M-C2	9050M-C3	9050M-C4	9050M-E1	9050M-E2	9050M-E3	9050M-E4
				Tilt	-	9051M-S	9051M-E	9051M-C1	9051M-C2	9051M-C3	9051M-C4	9051M-E1	9051M-E2	9051M-E3	9051M-E4
				Dlx Tilt	-	9052M-S	9052M-E	9052M-C1	9052M-C2	9052M-C3	9052M-C4	9052M-E1	9052M-E2	9052M-E3	9052M-E4
		Large	15 ½" – 21"	Non Tilt	-	9050L-S	9050L-E	9050L-C1	9050L-C2	9050L-C3	9050L-C4	9050L-E1	9050L-E2	9050L-E3	9050L-E4
				Tilt	-	9051L-S	9051L-E	9051L-C1	9051L-C2	9051L-C3	9051L-C4	9051L-E1	9051L-E2	9051L-E3	9051L-E4
				Dlx Tilt	-	9052L-S	9052L-E	9052L-C1	9052L-C2	9052L-C3	9052L-C4	9052L-E1	9052L-E2	9052L-E3	9052L-E4
MID	27" Black Nylon	Medium	20" – 27 ½"	Non Tilt	20" Adj Chrome	6300M	-	-	-	-	-	-	-	-	-
				Tilt	20" Adj Chrome	6301M	-	-	-	-	-	-	-	-	-
				Dlx Tilt	20" Adj Chrome	6302M	-	-	-	-	-	-	-	-	-
		Large	20" – 27 ½"	Non Tilt	20" Adj Chrome	6300	-	-	-	-	-	-	-	-	-
				Tilt	20" Adj Chrome	6301	-	-	-	-	-	-	-	-	-
				Dlx Tilt	20" Adj Chrome	6302	-	-	-	-	-	-	-	-	-
	27" Polished Aluminum	Medium	19" – 26 ½"	Non Tilt	20" Adj Chrome	9350M-S	9350M-E	9350M-C1	9350M-C2	9350M-C3	9350M-C4	9350M-E1	9350M-E2	9350M-E3	9350M-E4
				Tilt	20" Adj Chrome	9351M-S	9351M-E	9351M-C1	9351M-C2	9351M-C3	9351M-C4	9351M-E1	9351M-E2	9351M-E3	9351M-E4
				Dlx Tilt	20" Adj Chrome	9352M-S	9352M-E	9352M-C1	9352M-C2	9352M-C3	9352M-C4	9352M-E1	9352M-E2	9352M-E3	9352M-E4
		Large	19" – 26 ½"	Non Tilt	20" Adj Chrome	9350L-S	9350L-E	9350L-C1	9350L-C2	9350L-C3	9350L-C4	9350L-E1	9350L-E2	9350L-E3	9350L-E4
				Tilt	20" Adj Chrome	9351L-S	9351L-E	9351L-C1	9351L-C2	9351L-C3	9351L-C4	9351L-E1	9351L-E2	9351L-E3	9351L-E4
				Dlx Tilt	20" Adj Chrome	9352L-S	9352L-E	9352L-C1	9352L-C2	9352L-C3	9352L-C4	9352L-E1	9352L-E2	9352L-E3	9352L-E4
TALL	27" Black Nylon	Medium	24" – 34"	Non Tilt	20" Adj Chrome	6500M	-	-	-	-	-	-	-	-	-
				Tilt	20" Adj Chrome	6501M	-	-	-	-	-	-	-	-	-
				Dlx Tilt	20" Adj Chrome	6502M	-	-	-	-	-	-	-	-	-
		Large	24" – 34"	Non Tilt	20" Adj Chrome	6500	-	-	-	-	-	-	-	-	-
				Tilt	20" Adj Chrome	6501	-	-	-	-	-	-	-	-	-
				Dlx Tilt	20" Adj Chrome	6502	-	-	-	-	-	-	-	-	-
	27" Polished Aluminum	Medium	21 ½" – 31 ½"	Non Tilt	20" Adj Chrome	9550M-S	9550M-E	9550M-C1	9550M-C2	9550M-C3	9550M-C4	9550M-E1	9550M-E2	9550M-E3	9550M-E4
				Tilt	20" Adj Chrome	9551M-S	9551M-E	9551M-C1	9551M-C2	9551M-C3	9551M-C4	9551M-E1	9551M-E2	9551M-E3	9551M-E4
				Dlx Tilt	20" Adj Chrome	9552M-S	9552M-E	9552M-C1	9552M-C2	9552M-C3	9552M-C4	9552M-E1	9552M-E2	9552M-E3	9552M-E4
		Large	21 ½" – 31 ½"	Non Tilt	20" Adj Chrome	9550L-S	9550L-E	9550L-C1	9550L-C2	9550L-C3	9550L-C4	9550L-E1	9550L-E2	9550L-E3	9550L-E4
				Tilt	20" Adj Chrome	9551L-S	9551L-E	9551L-C1	9551L-C2	9551L-C3	9551L-C4	9551L-E1	9551L-E2	9551L-E3	9551L-E4
				Dlx Tilt	20" Adj Chrome	9552L-S	9552L-E	9552L-C1	9552L-C2	9552L-C3	9552L-C4	9552L-E1	9552L-E2	9552L-E3	9552L-E4

Updated August 20, 2025

ACCESSORIES

ARMS

Standard & CR:
 A5 - Models that end in 0 & 2
 AA - Models that end in 1

ESD & ESD/CR:
 A8 - Models that end in 0 & 2
 AAE - Models that end in 1



CASTERS

Casters add 1" to seat height range.



HARD FLOOR CASTERS

Standard: 3850S/5
 6000 only: 4550S/5
 ESD: CARD5S



CARPET CASTERS

Standard: 3850/5
 6000 only: 4550/5



SPECIALTY CASTERS

INTERVAL BRAKING
 Standard: IBCS
 ESD: IBCS-ESD

REVERSE BRAKING
 Standard: RBCS