



UPHOLSTERED CHAIRS



4000 Series WESTMOUND SERIES



FEATURED MODEL
4500-F-BLK

DIMENSIONS

SEAT
20" W x 17" D
2 1/2" Thick

BACK
16" W x 10" H
2" Thick

UPHOLSTERY OPTIONS

STANDARD



BLACK



GRAY



BLACK VINYL



NAVY BLUE



ROYAL BLUE



BLUE VINYL

CR & ESD/CR



BLACK VINYL



BLUE VINYL

BUILT TO ORDER

Each chair is configured to your exact specifications – choice of upholstery, arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model # w/Fabric	Standard Model # w/Vinyl	Cleanroom ISO 6 Model #	ESD/CR ISO 6 Model #
DESK	25" Black Nylon	16 ½" - 21 ½"	Non Tilt	-	4000-F	4000-V	-	-
			Tilt	-	4001-F	4001-V	-	-
			Dlx Tilt	-	4002-F	4002-V	-	-
	25" Polished Aluminum	15 ½" - 20 ½"	Non Tilt	-	-	-	4050C3	4050E3
			Tilt	-	-	-	4051C3	4051E3
			Dlx Tilt	-	-	-	4052C3	4052E3
MID	27" Black Nylon	19 ½" - 27"	Non Tilt	18" Adj. Chrome	4300-F	4300-V	-	-
			Tilt	18" Adj. Chrome	4301-F	4301-V	-	-
			Dlx Tilt	18" Adj. Chrome	4302-F	4302-V	-	-
	27" Polished Aluminum	19 ½" - 27"	Non Tilt	18" Adj. Chrome	-	-	4350C3	4350E3
			Tilt	18" Adj. Chrome	-	-	4351C3	4351E3
			Dlx Tilt	18" Adj. Chrome	-	-	4352C3	4352E3
	22" Black Tubular Steel	20" - 25"	Non Tilt	19" Welded Chrome	4200-F	4200-V	-	-
			Tilt	19" Welded Chrome	4201-F	4201-V	-	-
			Dlx Tilt	19" Welded Chrome	4202-F	4202-V	-	-
	22" Chrome Tubular Steel	19 ½" - 24 ½"	Non Tilt	19" Welded Chrome	-	-	4210C3	4210E3
			Tilt	19" Welded Chrome	-	-	4211C3	4211E3
			Dlx Tilt	19" Welded Chrome	-	-	4212C3	4212E3
TALL	27" Black Nylon	22 ½" - 32 ½"	Non Tilt	18" Adj. Chrome	4500-F	4500-V	-	-
			Tilt	18" Adj. Chrome	4501-F	4501-V	-	-
			Dlx Tilt	18" Adj. Chrome	4502-F	4502-V	-	-
	27" Polished Aluminum	22" - 32"	Non Tilt	18" Adj. Chrome	-	-	4550C3	4550E3
			Tilt	18" Adj. Chrome	-	-	4551C3	4551E3
			Dlx Tilt	18" Adj. Chrome	-	-	4552C3	4552E3
	22" Black Tubular Steel	25" - 30"	Non Tilt	19" Welded Chrome	4600-F	4600-V	-	-
			Tilt	19" Welded Chrome	4601-F	4601-V	-	-
			Dlx Tilt	19" Welded Chrome	4602-F	4602-V	-	-
	22" Chrome Tubular Steel	24 ½" - 29 ½"	Non Tilt	19" Welded Chrome	-	-	4610C3	4610E3
			Tilt	19" Welded Chrome	-	-	4611C3	4611E3
			Dlx Tilt	19" Welded Chrome	-	-	4612C3	4612E3

FEATURED MODEL

4351C3-BLU



Updated July 25, 2025

ACCESSORIES

BACK UPGRADE
Medium Back: (MDB)



CASTERS
Casters add 1" to seat height range.



HARD FLOOR CASTERS
Standard: 5-star: 3850S/5
Tubular: CADS/5
ESD: CARD5S



CARPET CASTERS
Standard: 5-star: 3850/5
Tubular: CAD/5



SPECIALTY CASTERS
INTERVAL BRAKING
Standard: IBCS
ESD: IBCS-ESD

REVERSE BRAKING
Standard: RBCS