

# PendoTECH® PressureMAT® DPG Handheld Pressure Monitor

Cole-Parmer®



PendoTECH PressureMAT DPG is a handheld digital pressure monitor designed to provide precise, real-time readings from PendoTECH Single-Use Pressure Sensors™. Engineered for ease of use, it operates on a 9V battery with an auto shutoff feature after 10 minutes to extend power life. The one-touch tare function allows for quick zeroing to atmospheric pressure, while the min/max display buttons provide instant access to pressure range data.



Scan the QR code for more information on PendoTECH products.

## Specification and Ordering Table

No. of Pressure Sensor Input Channels	Pressure Input Range	Resolution	Accuracy	Battery Life	Power	Item Number
1	-11.5 to 75.0 psi	0.1 psi	±2% of reading from 0 to 6 psi, ±3% of reading from 6 to 30 psi	Approx. 14 hours	9V battery	<a href="#">59900-09</a>

## APPLICATIONS

- Perfect for various biopharmaceutical processes, including filtration, bioreactors, and chromatography
- Ideal for general-purpose, laboratory, and single-use applications

## FEATURES/BENEFITS

- Seamless integration with PendoTECH Single-Use Pressure Sensors™
- No calibration required—reads standardized sensor output directly
- Compact and battery-operated for convenient, on-the-go pressure monitoring
- Minimum/maximum pressure display with one-touch tare to atmospheric pressure function
- Updates >2X per second
- Monitor features 12-ft reusable cable to easily connect to pressure sensors
- Free technical application support available to assist

USA +1.800.323.4340  
+1.847.549.7600  
Canada +1.800.363.5900  
China 86.21.5109.9909  
India +1.800.266.1244

UK +44 (0) 1480.272279  
+33 (0) 1.87.170142\*  
+49 (0) 937.792030\*  
Italy +39.02.84349215  
All others +1.847.549.7600

Cole-Parmer®  
[coleparmer.com](http://coleparmer.com)

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.