

Cole-Parmer®

Click or scan for our
full product offering.



PIPETTES

MINI GUIDE

Precision You Can Count On

Find essential information on our top-selling pipette products, compatible tips, and must-have accessories, plus resources to help you make the best selection for your lab.



Top-Selling Pipette Products

Available now at [coleparmer.com](https://www.coleparmer.com)

ALWAYS
IN STOCK

From simple transfers to precise analytical dispensing, pipettes are the backbone of accurate liquid handling. In this quick-reference guide, you'll find Cole-Parmer's pipettes and accessories, built to deliver precision, reliability, and reproducible results across research, diagnostics, and quality-control applications.

Each of these customer favorites combines ergonomic design, trusted accuracy, and reliable performance. Choose the model that best matches your workflow and volume range. Each pipette is compatible with Cole-Parmer pipette tips for reliable fit and contamination control.

Adjustable-Volume Pipettor

Universal pipette controller with adjustable aspiration speed. Ideal for cell culture and serological pipettes.

Item# 24501-07



100 mL Disposable Serological Pipettes

Graduated serological pipettes used in cell handling and large-volume liquid transfers.

Item# 04395-22



10 mL Polystyrene Standard Sterile Serological Pipettes

Precision-graduated for exact volume measurement, commonly used in QC labs.

Item# 13002-30



230 mm Sterile Plastic Pasteur Pipettes

Ideal for delicate liquid transfer and tissue culture work.

Item# 04395-12



Omega Zen® Pipette Controller

Ergonomic pipette controller with long battery life and color-coded design.


Item# 25300-96



7.5 mL Graduated Large Bulb Transfer Pipette

Disposable, sterile, and accurate. Used across diagnostics and clinical labs.

Item# 06226-63



Pipette Tips & Accessories



To complement your pipettes, we offer a wide range of tips and tools for better precision and contamination control.

Category	Description/Features	Volume Range/Specs	Item No./Pack Size
Cole-Parmer® General-Purpose Pipette Tips	Virgin PP; precision-molded; contamination-free; steam autoclavable at 121 °C/15 min.	1 to 5 mL 1 to 10 mL	25711-71 (2000 Tips/Bag) 25711-73 (1000 Tips/Bag)
Cole-Parmer® Sterile Graduated Tips (Standard Racks)	FDA-approved PP; low-retention; noncytotoxic; PE filters prevent aerosols; free of heavy metals.	0.1 to 10 µL 2 to 20 µL 10 to 100 µL 10 to 100 µL 20 to 200 µL 100 to 1000 µL 100 to 1000 µL	24501-49 (10 Racks; 960/Pack) 24502-00 Filter (10 Racks; 960/Pack) 24502-18 Filter (10 Racks; 960/Pack) 24502-19 Filter, Low Retention (10 Racks; 960/Pack) 24502-30 Standard Retention (10 Racks; 960/Pack) 24502-68 (6 Racks; 576/Pack) 16350-19 Filter, Low Retention (6 Racks; 576/Pack)
Cole-Parmer® Sterile Long Graduated Tips (Aerosol Barrier)	High-transparency medical-grade PP; extended length; available in standard or low-retention, filtered versions.	0.1 to 10 µL 20 to 200 µL 20 to 200 µL 20 to 200 µL 20 to 200 µL 100 to 1000 µL 100 to 1250 µL 100 to 1000 µL	24501-67 (10 Racks; 960/Pack) 24502-50 Standard Retention (10 Racks; 960/Pack) 24502-52 Low Retention (10 Racks; 960/Pack) 24502-53 Filter, Standard Retention (10 Racks; 960/Pack) 24502-54 Filter, Low Retention (10 Racks; 960/Pack) 24502-88 Standard Retention (6 Racks; 576/Pack) 16350-23 Filter, Standard Retention (6 Racks; 576/Pack) 24502-92 Filter, Low Retention (6 Racks; 576/Pack)
Cole-Parmer® Trace Metal Analysis Tips	Certified trace-metal-free; RNase/DNase-free; precision-molded PP for airtight fit.	1 to 200 µL 101 to 1000 µL	25713-02 (10 Racks; 96/Tips) 25713-00 (10 Racks; 100/Tips)
Cole-Parmer® Omega Zen® Pipette Controller	Eight speeds from drip dispense to 8.3 mL/s; UV-resistant housing; ergonomic design; for 1 to 100 mL pipettes.	—	25300-96 (Blue) 25300-98 (Gray)

Additional Pipette Accessories

Basins

Ideal for multichannel use and reagent transfer.



Stands and Racks

Organize and protect your pipettes.



Cleaning Products

Maintain accuracy and compliance.



Selection Help & Calibration Services

Not sure which pipette fits your workflow? Our experts can help you choose the right pipette based on application type, frequency of use, and volume range.

Our support includes:

- ✔ Application-based pipette recommendations
- ✔ Manual versus electronic pipette guidance
- ✔ Mail-in ISO-certified calibration
- ✔ Multi-brand support and compliance documentation

Stay compliant and accurate.

Proper calibration reduces risk of error and ensures your data integrity meets regulatory standards.

Scan to learn more or request service.



Explore More Liquid Handling Solutions

Find our full range of pipettes, tips, and controllers at [coleparmer.com/c/pipettes-and-pipettors](https://www.coleparmer.com/c/pipettes-and-pipettors).

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®
[coleparmer.com](https://www.coleparmer.com)

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.