

## Cole-Parmer® PVC 2-Stop Pump Tubing

Stopped tubing ensures a perfect fit every time. Stops hold tubing in pump head for optimal tension, resulting in reliable pumping and repeatable flow rates. It delivers accurate and interference-free analytical results. Made from phthalate-free PVC, this tubing exhibits great resistance to a wide range of common chemicals, ensuring dependable performance for many routine applications. Anti-leaching characteristics minimize the risk of interferences or false positives, ensuring accurate and reliable results.



### CERTIFICATION

USP Class VI and USP 37-NF32 2014 compliant

### PVC 2-STOP PUMP TUBING SIZE



### APPLICATIONS

- Perfect for general lab use, food contact, and use in peristaltic pumps
- Ideal for general-purpose, laboratory, and single-use applications

### FEATURES/BENEFITS

- Two tubing stops are color-coded for easy size identification
- Sterilize via autoclave, gamma irradiation (with some discoloration), or ethylene oxide
- Withstands a wide temperature range of -50 to 74 °C (-58 to 165 °F)
- Flexible tubing with a 59 Shore A durometer
- Transparent tubing—perfect for easily viewing fluid flow
- Tubing does not contain SVHCs and is fully REACH and RoHS compliant
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

**Cole-Parmer®**  
coleparmer.com

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

## Specification and Ordering Table

Dimensions: mm (in.)			Color-Coded Stops	Tubes/Pack	Item Number
Tubing ID	Length Between Stops	Tubing Length			
0.13 (0.005")	150 (5.9")	455 (17.9")	Orange/Black	12	<a href="#">50137-03</a>
0.19 (0.0075")	150 (5.9")	455 (17.9")	Orange/Red	12	<a href="#">50137-06</a>
0.25 (0.001")	150 (5.9")	455 (17.9")	Orange/Blue	12	<a href="#">50137-09</a>
0.38 (0.015")	150 (5.9")	455 (17.9")	Orange/Green	12	<a href="#">50137-13</a>
0.51 (0.02")	150 (5.9")	455 (17.9")	Orange/Yellow	12	<a href="#">50137-17</a>
0.64 (0.025")	150 (5.9")	455 (17.9")	Orange/White	12	<a href="#">50137-21</a>
0.76 (0.03")	150 (5.9")	455 (17.9")	Black/Black	12	<a href="#">50137-25</a>
0.89 (0.035")	150 (5.9")	455 (17.9")	Orange/Orange	12	<a href="#">50137-29</a>
1.02 (0.04")	150 (5.9")	455 (17.9")	White/White	12	<a href="#">50137-33</a>
1.14 (0.045")	150 (5.9")	455 (17.9")	Red/Red	12	<a href="#">50137-37</a>
1.3 (0.05")	150 (5.9")	455 (17.9")	Gray/Gray	12	<a href="#">50137-41</a>
1.42 (0.056")	150 (5.9")	455 (17.9")	Yellow/Yellow	12	<a href="#">50137-45</a>
1.52 (0.06")	150 (5.9")	455 (17.9")	Yellow/Blue	12	<a href="#">50137-47</a>
1.65 (0.065")	150 (5.9")	455 (17.9")	Blue/Blue	12	<a href="#">50137-50</a>
1.75 (0.07")	150 (5.9")	455 (17.9")	Blue/Green	12	<a href="#">50137-53</a>
1.85 (0.073")	150 (5.9")	455 (17.9")	Green/Green	12	<a href="#">50137-55</a>
2.06 (0.08")	150 (5.9")	455 (17.9")	Purple/Purple	12	<a href="#">50137-58</a>
2.29 (0.09")	150 (5.9")	455 (17.9")	Purple/Black	12	<a href="#">50137-61</a>
2.54 (0.1")	150 (5.9")	455 (17.9")	Purple/Orange	12	<a href="#">50137-63</a>
2.79 (0.11")	150 (5.9")	455 (17.9")	Purple/White	12	<a href="#">50137-66</a>
3.18 (0.125")	150 (5.9")	455 (17.9")	Black/White	12	<a href="#">50137-68</a>