

Cole-Parmer® Solvent-Resistant PVC 3-Stop Pump Tubing

Stopped tubing ensures a perfect fit every time. Stops hold tubing in the pump head for optimal tension, resulting in reliable pumping and repeatable flow rates. Three stops give you two tubing sections instead of just one. When one tubing section wears, a new section is ready to use. Use solvent-resistant PVC tubing with aromatic oils, solvents, and petroleum products. It exhibits similar chemical resistance characteristics to Viton® tubing, but at a lower cost, making it an excellent alternative. The phthalate-free and anti-leaching characteristics minimize the risk of interferences or false positives, ensuring accurate and reliable results. Bright yellow translucent tubing helps differentiate from standard PVC stop tubing.



CERTIFICATION

USP Class VI compliant

SOLVENT-RESISTANT PVC 3-STOP TUBING SIZE



APPLICATIONS

- Perfect for general lab use, industrial applications like inks and oils, and use in peristaltic pumps
- Ideal for general-purpose, laboratory, and single-use applications

FEATURES/BENEFITS

- Three tubing stops are color-coded for easy size identification
- Sterilize via autoclave or ethylene oxide
- Withstands a wide temperature range of -50 to 74 °C (-58 to 165 °F)
- Flexible tubing with a 61 Shore A durometer
- Yellow transparent tubing—perfect for visual confirmation of fluid flow
- Tubing does not contain SVHCs and is phthalate-free
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®
coleparmer.com

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

Specification and Ordering Table

Dimensions: mm (in.)			Color-Coded Stops	Tubes/Pack	Item Number
Tubing ID	Length Between Stops	Tubing Length			
1.3 (0.05")	82 (3.2")	455 (17.9")	Gray/Gray/Gray	12	50138-00
2.54 (0.1")	82 (3.2")	455 (17.9")	Purple/Orange/Purple	12	50138-19
2.79 (0.11")	82 (3.2")	455 (17.9")	Purple/White/Purple	12	50138-23