

## Cole-Parmer® Sterile WFI Samplers

Minimize the risk of sample contamination with sterile WFI samplers. Samplers feature tubing with a polypropylene (PP) sanitary fitting and fused polypropylene gasket. This sanitary connection and fused gasket allow for sample collection without having to come in contact with the fitting, removing significant contamination risk. Samplers come gamma irradiated for microbial control and doublebagged in an easy-peel pouch.



### CERTIFICATION

ASME-BPE, USP Class VI, FDA 21 CFR 177.1520, and RoHS compliant

**WARNING:** This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

### APPLICATIONS

- Single use
- Pharmaceutical
- Lab research

### FEATURES/BENEFITS

- One-piece design with sanitary fitting provides clean, hassle-free connection
- Gamma irradiated for sterility
- Doublebagged in an easy-peel, low-permeability pouch
- Assembled in ISO Class 7 cleanroom
- ASME-BPE, USP Class VI, FDA 21 CFR 177.1520, and RoHS compliant
- Animal-derived component free (ADCF)

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

**Cole-Parmer®**  
[coleparmer.com](http://coleparmer.com)

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

## Specification and Ordering Table

Tri-Clamp Fitting	Tubing Material	Dimensions: in. (mm)			Tubing Durometer	Length: in. (cm)	Item Number	No. Per Pack
		Tubing ID	Tubing OD	Tubing Wall				
3/4"	TPE	1/4" (6.4)	7/16" (11)	3/32" (2.4)	68A	18" (46)	<a href="#">50142-42</a>	10
3/4"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	68A	36" (91)	<a href="#">50142-43</a>	10
1-1/2"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	68A	18" (46)	<a href="#">50142-44</a>	10
1-1/2"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	68A	36" (91)	<a href="#">50142-45</a>	10
3/4"	Platinum-Cured Silicone	1/4" (6.4)	7/16" (11)	3/32" (2.4)	50A	18" (46)	<a href="#">50142-46</a>	10
3/4"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	50A	36" (91)	<a href="#">50142-47</a>	10
1-1/2"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	50A	18" (46)	<a href="#">50142-48</a>	10
1-1/2"		1/4" (6.4)	7/16" (11)	3/32" (2.4)	50A	36" (91)	<a href="#">50142-49</a>	10