


## Cole-Parmer® Tri-Clamp Sight Gauges Polysulfone



Get an unobstructed view of your sample on a large, clear polysulfone sight gauge. The large tubular window offers a view from multiple angles.

The sight gauges withstand temperatures ranging from -29 to 155 °C (-20 to 240 °F) and exhibit excellent chemical resistance. Simply use sanitary Tri-Clamp fittings and clamps for leakproof, sterile connections.



### CERTIFICATION

ASME-BPE, USP Class VI, ISO 10993, and RoHS compliant

**WARNING:** This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

### APPLICATIONS

- Critical bioprocessing, food processing, and chemical processing applications

### FEATURES/BENEFITS

- Polysulfone (PSU) offers superior optical clarity
- Sanitary quick clamp connections
- Sterilize by gamma irradiation or steam
- Visually confirm flow, color, and clarity of your process media
- Animal-derived ingredient free (ADIF) and animal-derived component free (ADCF)

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

**Cole-Parmer®**

[coleparmer.com](http://coleparmer.com)

\*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

## Specification and Ordering Table

Material	Tube Inner Diameter (ID): in. (mm)	End Fitting	Length: in. (mm)	Item Number
Polysulfone	0.48" (12.2)	3/4" Sanitary Connection	6" (152.4)	<a href="#">50142-83</a>
Polysulfone	0.86" (21.8)	1" Sanitary Connection	6" (152.4)	<a href="#">50142-84</a>
Polysulfone	1.36" (34.5)	1-1/2" Sanitary Connection	6" (152.4)	<a href="#">50142-85</a>
Polysulfone	1.86" (47.2)	2" Sanitary Connection	6" (152.4)	<a href="#">50142-86</a>
Polysulfone	2.36" (59.9)	2-1/2" Sanitary Connection	6" (152.4)	<a href="#">50142-87</a>
Polysulfone	2.86" (72.6)	3" Sanitary Connection	6" (152.4)	<a href="#">50142-88</a>