

Cole-Parmer® Tube Sinkers Kynar® PVDF



Connect a tube sinker to your tubing to keep it at the bottom of your container. The flow-through design provides efficient emptying or filling by pumps or dispensers.

A slight recess at the bottom of the sinker prevents it from suctioning against the container. The monobarb fitting accepts flexible tubing.



CERTIFICATION

ASME-BPE, USP Class VI, and RoHS compliant

WARNING: This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

APPLICATIONS

- Bio research, pharmaceutical, and life sciences applications

FEATURES/BENEFITS

- Flow-through design—perfect for filling and dispensing
- Hose barb fitting accepts flexible tubing
- Animal-derived ingredient free (ADIF) and animal-derived component free (ADCF)
- Sterilize by autoclave, gamma irradiation, X-ray, or EtO
- Operating temperature range of -62 to 135 °C (-80 to 275 °F)
- Translucent Kynar PDVF construction offers superior chemical resistance

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®

coleparmer.com

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

Specification and Ordering Table

Connection Type	Tubing ID: in. (mm)	Outside Diameter (OD): in. (mm)	Length: in. (mm)	Item Number
Hose Barb	3/16" (4.8)	0.5" (12.7)	1.28" (32.5)	50142-89
Hose Barb	1/4" (6.4)	0.53" (13.5)	1.56" (39.6)	50142-90
Hose Barb	5/16" (8)	0.63" (16)	1.63" (41.4)	50142-91
Hose Barb	3/8" (9.5)	0.69" (17.5)	2.56" (65)	50142-92
Hose Barb	1/2" (12.7)	0.88" (22.4)	2.5" (63.5)	50142-93
Hose Barb	3/4" (19.1)	1.13" (28.7)	3.12" (79.3)	50142-94