

Cole-Parmer®

Versilon® SPT-50 Platinum-Cured Silicone Tubing

Versilon® SPT-50 platinum-cured silicone tubing features exceptionally smooth inner surface, minimal extractables, and does not transmit taste or odor, making it perfect for transferring high-purity fluids. Excellent flexibility, high tear resistance, and non-tacky outer surface make this tubing ideal for peristaltic pump applications.



CERTIFICATION

FDA and NSF-51

APPLICATIONS

- Perfect for peristaltic pumping, food processing, and high-temperature filling
- Ideal for general-purpose, laboratory, and single-use applications

FEATURES/BENEFITS

- Smooth inner surface inhibits protein binding and bacterial growth for easy sterilization and sanitation
- Non-tacky outer surface increases pump life
- Sterilize via autoclave, ethylene oxide (EtO), or gamma irradiation
- Flexible tubing with a 50 Shore A durometer
- Translucent tubing provides good clarity
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	+86.21.5109.9909
India	+1.800.266.1244

UK	+44 (0) 1480.272279
	+33 (0) 1.87.170142*
	+49 (0) 937.792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Cole-Parmer®

coleparmer.com

*Inquiries from Germany and France are now handled in our St. Neots office by native-speaking experts.

Specification and Ordering Table

Dimensions: in. (mm)			Item Number	Reel Length (ft)
Tubing ID	Tubing OD	Wall		
1/32" (0.8)	3/32" (2.4)	1/32" (0.8)	00123-38	50
1/16" (1.6)	1/8" (3.2)	1/32" (0.8)	00123-39	50
1/16" (1.6)	3/16" (4.8)	1/16" (1.6)	00123-40	50
3/32" (2.4)	5/32" (4)	1/32" (0.8)	00123-41	50
3/32" (2.4)	7/32" (5.6)	1/16" (1.6)	00123-42	50
1/8" (3.2)	3/16" (4.8)	1/32" (0.8)	00123-43	50
1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	00123-44	50
5/32" (4)	7/32" (5.6)	1/32" (0.8)	00123-45	50
3/16" (4.8)	1/4" (6.4)	1/32" (0.8)	00123-46	50
3/16" (4.8)	5/16" (8)	1/16" (1.6)	00123-47	50
3/16" (4.8)	3/8" (9.5)	3/32" (2.4)	00123-48	50
3/16" (4.8)	7/16" (11)	1/8" (3.2)	00123-49	50
1/4" (6.4)	5/16" (8)	1/32" (0.8)	00123-50	50
1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	00123-51	50
1/4" (6.4)	7/16" (11)	3/32" (2.4)	00123-52	50
1/4" (6.4)	1/2" (12.7)	1/8" (3.2)	00123-53	50
5/16" (8)	7/16" (11)	1/16" (1.6)	00123-54	50
5/16" (8)	1/2" (12.7)	3/32" (2.4)	00123-55	50
3/8" (9.5)	1/2" (12.7)	1/16" (1.6)	00123-56	50
3/8" (9.5)	9/16" (14.3)	3/32" (2.4)	00123-57	50
3/8" (9.5)	5/8" (15.9)	1/8" (3.2)	00123-58	50
7/16" (11)	9/16" (14.3)	1/16" (1.6)	00123-59	50
7/16" (11)	5/8" (15.9)	3/32" (2.4)	00123-60	50
1/2" (12.7)	5/8" (15.9)	1/16" (1.6)	00123-61	50
1/2" (12.7)	11/16" (17.5)	3/32" (2.4)	00123-62	50
1/2" (12.7)	3/4" (19.1)	1/8" (3.2)	00123-63	50
5/8" (15.9)	13/16" (20.6)	3/32" (2.4)	00123-64	50
5/8" (15.9)	7/8" (22.2)	1/8" (3.2)	00123-65	50
3/4" (19.1)	1" (25.4)	1/8" (3.2)	00123-66	50
1" (25.4)	1-1/4" (31.8)	1/8" (3.2)	00123-67	50
1-1/4" (31.8)	1-1/2" (38.1)	1/8" (3.2)	00123-68	50
1-1/2" (38.1)	2" (50.8)	1/4" (6.4)	00123-69	50