

4" (101mm) Pressure Chart Recorder



Specifications

Ambient Operating RH Conditions : 0-95% RH non-condensing

Ambient Operating Temperature Conditions: -22 to 122F (-30 to 50C)

Battery Life (Avg): 1 Year

Calibration Options: N100, N300

Channels: CH1: Pressure

Chart Rotation Speed: 24 Hour

Dimensions: 6.25 x 6 x 2.9in

Enclosure: Velox PBT NEMA 4X with Polycarbonate Door Window (Weather/Water Resistant)

Fitting: 1/4" NPT Thread, 5/8" Hex

IP Rating: 66

Included Accessories: One AA Battery, Red Pen and Quick Start Guide. *Charts sold separately.

Mounting Options: Stem or Wall Mount (With Keyhole)

Power Source: Battery; One AA Battery (User Replaceable)

Pressure Accuracy: 2% of Full Scale

Pressure Range: 0 to 500PSI

Response Time: 1 Second

Unit Weight: 1.8 lbs

Units/Pkg: 1

Warranty: 12-Month Limited

Accessories PW479



Pressure Kit
Pressure Fitting Accessory Kit



Pressure Pigtail
Steam Pressure Pigtail



Hydrant Kit
Fire Hydrant Adapter Kit



AA Battery
AA Alkaline Battery



Pressure Filter Kit
Filter Kit includes Snubber

Calibrations

N100 1-Point NIST Traceable Calibration

N300 3-Point NIST Traceable Calibration