

## 8" (203mm) Pressure Chart Recorder



---

## Specifications

**Ambient Operating RH Conditions :** 0-95% RH non-condensing

**Ambient Operating Temperature Conditions:** -22 to 122F (-30 to 50C)

**Battery Life (Avg):** 1 Year

**Calibration Options:** N100, N300

**Channels:** CH1: Pressure

**Chart Rotation Speed:** 7 Day

**Dimensions:** 3.6 x 10.3 x 9.5in

**Enclosure:** Plastic NEMA 4X Case with Window in Door

**Fitting:** 1/4" NPT Thread, 5/8" Hex

**IP Rating:** 66

**Included Accessories:** One AA Battery, Red Pen and Quick Start Guide. \*Charts sold separately.

**Mounting Options:** Stem or Wall Mount (With Keyhole)

**Power Source:** Battery; One AA Battery (User Replaceable)

**Pressure Accuracy:** 2% of Full Scale

**Pressure Range:** 0 to 100PSI

**Response Time:** 1 to 5 Seconds

**Unit Weight:** 9 lbs

**Units/Pkg:** 1

**Warranty:** 12-Month Limited

## Accessories PW860



**Pressure Kit**  
Pressure Fitting Accessory Kit



**Pressure Pigtail**  
Steam Pressure Pigtail



**Hydrant Kit**  
Fire Hydrant Adapter Kit



**AA Battery**  
AA Alkaline Battery



**Pressure Filter Kit**  
Filter Kit includes Snubber

---

## Calibrations

**N100** 1-Point NIST Traceable Calibration

**N300** 3-Point NIST Traceable Calibration