

3" (76mm) Temperature Chart Recorder



Specifications

Ambient Operating RH Conditions : 0-95% RH non-condensing

Ambient Operating Temperature Conditions: -22 to 122F (-30 to 50C)

Battery Life (Avg): 2 Years

Calibration Options: N100, N300, N400

Channels: CH1: Temperature

Chart Rotation Speed: 24 Hour or 7 Day

Dimensions: 2.2 x 3.7 x 3.7in

Enclosure: Black ABS and Polycarbonate

IP Rating: 20

Included Accessories: One AA Battery, Red Pen and Quick Start Guide. *Charts sold separately.

Mounting Options: Free Standing, Wall Mounted or Suspended

Power Source: Battery; One AA Battery (User Replaceable)

Response Time: 11 Minutes to 63% of Full Scale (in air moving 5' per second)

Temperature Accuracy: +/-2F from 4 to 50F (+/-1C from -15 to 10C)

Temperature Range: 4 to 50F (-15 to 10C)

Temperature Sensor: Precise spiral wound bi-metallic strip transducer

Unit Weight: 1 lb

Units/Pkg: 1

Warranty: 12-Month Limited

Accessories SC377



Wall Mount Case
Small Locking Wall Mount Case



AA Battery
AA Alkaline Battery

Calibrations

N100 1-Point NIST Traceable Calibration

N300 3-Point NIST Traceable Calibration

N400 3-Point Ultima NIST A2LA Accredited Calibration