

Wax Dispensers

Models 145600, 145600-2, 1456XL, 1456XL-2



Wax Dispenser Model 145600 and 145600-2

Dimensions (Diameter x Height)	8.50" x 16"
Temperature Range	40° C to 75° C +/- 2° C
Electrical 145600	115 V, 50/60 Hz, 250 W (UL/CSA)
145600-2	230 V, 50/60 Hz, 250 W (CE)

Features:

- 5L (1.25 Gal) capacity
- Heated valve ensures a consistent flow of molten wax
- Stainless steel outer casing
- Aluminum inner reservoir provides excellent thermal transfer and temperature control
- Dispenser valve allows precise control of flowing wax and can be locked in the open position if desired
- Inner reservoir screen helps to prevent large particulate from clogging the dispenser valve
- Rapid warm-up with an advanced safety over-temperature cut-off
- 2 Year warranty



145600 Wax Dispenser

Large Wax Dispenser Model 1456XL and 1456XL-2

Dimensions (W x L x H)	14" x 25.5" x 18.75"
Temperature Range	Ambient +5°C to 65°C
Default Temperature	55°C
Safety Cut off	88°C
Electrical 1456XL	115 V, 50/60 Hz, 750 W (UL/CSA)
1456XL-2	230 V, 50/60 Hz, 750 W (CE)

Features:

- 28L (7.4 Gal) capacity (largest on the market)
- Adaptive digital control system that melts wax quickly and maintains the ideal temperature
- Hot Start feature will automatically start the warming based on set time to eliminate waiting
- Bright easy to use digital display
- Stainless steel lid and wax chamber to resist corrosion
- Heated and filtered wax spigot to keep the wax flowing quickly
- Two-year warranty



1456XL Large Wax Dispenser