



## Borescopes

### Get better viewing of hard-to-reach places

See into hard-to-reach areas with flexible camera-tipped probe. View inspected area on bright LCD monitor. Adjustable LED light on camera illuminates dimly-lit spaces or adjusts down when viewing reflective surfaces to eliminate washout.

### Features

- ◆ View on external video device with TV-OUT hookup
- ◆ See even in dark environments with four adjustable LED lights
- ◆ 180° image rotation
- ◆ Stop replacing batteries—built-in Li-ion battery with USB charging
- ◆ Waterproof (IP67-rated) flexible camera probe

### Borescope model 20250-28

- ◆ Real-time viewing on 3" color LCD
- ◆ Selectable English or German languages

### Video borescope model 20250-27

- ◆ Real-time viewing on 3.2" color LCD
- ◆ Capture still and video images for playback on LCD, TV, or computer monitor
- ◆ Easy transfer of video and images to your PC with SD card or USB cable; date/time stamp
- ◆ 8 GB flash memory
- ◆ Selectable English, French, German, or Spanish languages

## Applications

- ◆ HVAC ductwork inspection
- ◆ Home inspection
- ◆ Automotive repair and vehicle inspection
- ◆ Industrial maintenance (see behind equipment, inspect welds, locate wiring)

## Includes

Probe, mirror, hook, magnet, carrying case, USB cable, DC 5V charger, video output cable, and rechargeable 3.7 V lithium-ion battery.



Description	Borescope	Video borescope
<b>Catalog number</b>	<b>MW-20250-28</b>	<b>MW-20250-27</b>
Probe diameter	2 <sup>1</sup> / <sub>32</sub> " (17 mm)	
Probe length	3.3 ft (1 m)	
Display	3.0" color LCD	3.2" color LCD
Resolution	960 x 240 pixels	320 x 240 pixels
Viewing angle	68°	
Viewing distance	2 to 6" (5 to 15 cm)	
Light source	Four adjustable LEDs	
Video format	—	MPEG4/3GP/AVI/ASF
Photo format	—	JPEG
Memory	—	Flash (8 GB), SD card (max 32 GB)
Working temperature	32 to 122°F (0 to 50°C)	32 to 131°F (0 to 55°C)
Dimensions (L x W x H)	3 <sup>15</sup> / <sub>16</sub> " x 3 <sup>3</sup> / <sub>4</sub> " x 9 <sup>1</sup> / <sub>4</sub> " (10 x 9.5 x 23.5 cm)	9 <sup>7</sup> / <sub>16</sub> " x 3 <sup>15</sup> / <sub>16</sub> " x 6 <sup>5</sup> / <sub>16</sub> " (24 x 10 x 16 cm)
Power	3.7 V lithium-ion battery	



### USA

#### Cole-Parmer

Toll-free: 800-323-4340  
Phone: 847-549-7600  
ColeParmer.com

#### Davis Instruments

Toll-free: 800-358-5525  
Phone: 847-327-2000  
Davis.com

#### For Calibration, InnoCal

Toll-free: 866-466-6225  
InnoCalSolutions.com

### CANADA

Toll-free: 800-363-5900  
Phone: 514-355-6100  
ColeParmer.ca

### UNITED KINGDOM

Free Phone: 0500-345-300  
Phone: 020-8574-7556  
ColeParmer.co.uk

### INDIA

Phone: 91-22-6716-222  
ColeParmer.in

### INTERNATIONAL CUSTOMERS

Call 847-549-7600  
ColeParmer.com/dealers