



DIGI-SENSE™
THE STANDARD IN PRECISION MEASUREMENT

Borescopes

Get better viewing of hard-to-reach places

See into hard-to-reach areas with flexible camera-tipped probe. View inspected area on bright LCD monitor. Adjustable LED light on camera illuminates dimly-lit spaces or adjusts down when viewing reflective surfaces to eliminate washout.

Features

- ♦ View on external video device with TV-OUT hookup
- ♦ See even in dark environments with four adjustable LED lights
- ♦ 180° image rotation
- ♦ Stop replacing batteries—built-in Li-ion battery with USB charging
- ♦ Waterproof (IP67-rated) flexible camera probe

Borescope model 20250-28

- ♦ Real-time viewing on 3" color LCD
- ♦ Selectable English or German languages

Video borescope model 20250-27

- ♦ Real-time viewing on 3.2" color LCD
- ♦ Capture still and video images for playback on LCD, TV, or computer monitor
- ♦ Easy transfer of video and images to your PC with SD card or USB cable; date/time stamp
- ♦ 8 GB flash memory
- ♦ Selectable English, French, German, or Spanish languages



Applications

- ◆ HVAC ductwork inspection
- ◆ Home inspection
- ◆ Automotive repair and vehicle inspection
- ◆ Industrial maintenance (see behind equipment, inspect welds, locate wiring)

Includes

Probe, mirror, hook, magnet, carrying case, USB cable, DC 5V charger, video output cable, and rechargeable 3.7 V lithium-ion battery.



Description	Borescope	Video borescope
Catalog number	MW-20250-28	MW-20250-27
Probe diameter	2 ¹ / ₃₂ " (17 mm)	
Probe length	3.3 ft (1 m)	
Display	3.0" color LCD	3.2" color LCD
Resolution	960 x 240 pixels	320 x 240 pixels
Viewing angle	68°	
Viewing distance	2 to 6" (5 to 15 cm)	
Light source	Four adjustable LEDs	
Video format	—	MPEG4/3GP/AVI/ASF
Photo format	—	JPEG
Memory	—	Flash (8 GB), SD card (max 32 GB)
Working temperature	32 to 122°F (0 to 50°C)	32 to 131°F (0 to 55°C)
Dimensions (L x W x H)	3 ¹⁵ / ₁₆ " x 3 ³ / ₄ " x 9 ¹ / ₄ " (10 x 9.5 x 23.5 cm)	9 ⁷ / ₁₆ " x 3 ¹⁵ / ₁₆ " x 6 ⁵ / ₁₆ " (24 x 10 x 16 cm)
Power	3.7 V lithium-ion battery	



USA

Cole-Parmer

Toll-free: 800-323-4340
Phone: 847-549-7600
ColeParmer.com

Davis Instruments

Toll-free: 800-358-5525
Phone: 847-327-2000
Davis.com

For Calibration, InnoCal

Toll-free: 866-466-6225
InnoCalSolutions.com

CANADA

Toll-free: 800-363-5900
Phone: 514-355-6100
ColeParmer.ca

UNITED KINGDOM

Free Phone: 0500-345-300
Phone: 020-8574-7556
ColeParmer.co.uk

INDIA

Phone: 91-22-6716-222
ColeParmer.in

INTERNATIONAL CUSTOMERS

Call 847-549-7600
ColeParmer.com/dealers