



## HM40 Handheld Humidity and Temperature Meter

		Spareparts		1	2	3	4
<b>Hand-held Humidity and Temperature Meter. Accuracy up to ±1.5% RH</b>		<b>HM40</b>					
hardware	1 Probe	<ul style="list-style-type: none"> <li><i>Fixed probe HMP113 (HM41) <sup>1</sup></i></li> <li><i>Remote Probe with Handle, HMP113+HM40HANDLE (HM45) <sup>1</sup></i></li> <li><i>4mm Thin Probe with Membrane Filter (HM42PROBE) <sup>2</sup></i></li> <li><i>Stainless Steel Probe with Sintered Filter (HM46PROBE) <sup>2</sup></i></li> <li><i>Stainless Steel Probe with Plastic Grid (HM46PROBE) <sup>2</sup></i></li> </ul>	A	B	C	D	E
	2 Batteries	<b>Alkaline Batteries (2 pcs)</b>	<b>1</b>				
		NiMH Rechargeable Batteries (4 pcs)	229247SP	2			
		External Battery Recharger with USB Connection, 2 Batteries	229249SP	3			
	3 Package	<b>Standard package</b>		<b>A</b>			
<b>Package for long probes</b>				<b>B</b>			
4 User's Guide Language	<b>English Manual HM40</b>			<b>B</b>			
	<b>No User's Guide</b>				<b>A</b>		

- 1) Select "Standard package" option for these probes  
2) Select "Package for long probes" option for these probes

<b>Note:</b>	<p><b>Selections in bold are included in the prices of the basic versions.</b></p> <ul style="list-style-type: none"> <li><i>Selections in italic are available at an extra price.</i></li> </ul>
<b>Links:</b>	<p><a href="#">User Guide</a></p> <p><a href="#">Datasheet</a></p> <p><a href="#">Filter Datasheet</a></p> <p><a href="#">Vaisala.com product page</a></p>

HM40	1	2	3	4
	<b>A</b>	<b>1</b>	<b>A</b>	<b>B</b>

### Accessories and spare parts

#### Indicator

- Battery Cover (3 pcs)
- Belt Clip (3 pcs)
- NiMH Rechargeable Batteries (4 pcs)
- External Battery Recharger with USB Connection and 2 Batteries
- Case for Short HM40 Probes (HM41, HM45)
- Case for Long HM40 Probes (HM42, HM46)
- Handheld Indicator

#### Standard probe (HM41)

- HMP113 probe for HM40
- Plastic Locking Bushing (3 pcs) for HMP113 Attachment to HM40 Indicator
- Plastic Grid Filter for HMP113 Probe
- Plastic Grid with Membrane Filter

#### HM42Probe (HM42)

- 4 mm Stainless Steel Measurement Probe for HM40
- Steel Grid Filter for HM42PROBE
- Membrane Tube Set (5 pcs) for HM42PROBE
- Rubber Sleeve Set (10 pcs) for HM42PROBE
- Calibration Adapter HM37067 (HM42)

#### HM45Probe (HM45)

- HMP113 probe for HM40
- Plastic Locking Bushing (3 pcs) for HMP113 Attachment to HM40 Indicator
- HM40 Handle and Cable
- Plastic Grid Filter for HMP113 Probe
- Plastic Grid with Membrane Filter

#### HM46Probe (HM46)

- 12 mm Stainless Steel Measurement Probe for HM40
- Sintered Bronze Filter, Female Thread
- Membrane Filter 12,0mm
- Plastic Grid HM4660
- Disposable Sleeve Set (50 pcs)
- Probe Holder HM36915

### Part number

- 225688SP
- 227710SP
- 229247SP
- 229249SP
- 235849SP
- DRW242351SP
- HM40INDI
- HMP113 (configuration: V00B2CIA0)
- DRW238590SP
- DRW236214SP
- 230727SP
- HM36915
- 19867HM
- 19858HM
- 19809HM
- HM37067
- HMP113 (configuration: V00B2CIA0)
- DRW238590SP
- HM40HANDLE
- DRW236214SP
- 230727SP
- HM46PROBE
- 0195
- 10159HM
- 6221
- 1558
- HM36915

