

...setting the standard again and again®

## Oakton® pH EcoTestrs™

Ideal for the classroom and on field trips!

- Economical pocket-sized pH meters
- Excellent education tool
- More accurate than litmus paper
- Waterproof housing — they even float!

OAKTON's new EcoTestrs are economical and easy to use. Ergonomically designed display allows students to view measurements at a glance. Simply dip and read—the orientation of the display means there's no need to turn your head or tilt the tester. They feature auto-buffer recognition for quick calibrations. Hold function locks in measured value. Auto-off function preserves batteries.

Each rugged tester has waterproof and dustproof housing for use in dirty and damp field conditions. Single-junction electrode is well-suited for general purpose applications. Recessed bulb with bulb guard protects against breakage.



### Specifications

**Operating temperature:** 32 to 122°F (0 to 50°C)

**Power:** four 1.5 V button cell batteries (included) Battery life: >300 hours

Model	EcoTestr pH 1	EcoTestr pH 2
Catalog number	WD-35423-00	WD-35423-10
Range	0.0 to 14.0 pH	
Resolution	0.1 pH	
Accuracy	±0.1 pH	
Temperature compensation	None	Automatic
Calibration	One-point	Up to three-point
Buffer recognition	Automatic: 4.0, 7.0, or 10.0	
Dimensions (W x H x D)	1 5/8" x 6 1/4" x 1 1/8" (3.9 x 15.9 x 2.9 cm)	

**Oakton quality at a great low price!**

**Available from most education supply distributors.**