

Statement on Restriction of Hazardous Substances in electrical and electronic equipment (RoHS) Directive

Directive 2011/65/EU and Amendment (EU) 2015/863 restrict the use of certain hazardous substances in electrical and electronic equipment above specific thresholds.

To the best of our knowledge the products of _____ and its affiliates do not intentionally contain substances identified in Directive 2011/65/EU or Amendment (EU) 2015/863 and therefore these substances are not expected to be present above limit values as listed below. The presence of analytically detectable traces, which have possibly been introduced via raw materials, auxiliaries and additives, cannot be excluded. Specific analyses to measure such traces have not been performed on raw materials or final products.

- Lead (limit value 0,1 %)
- Mercury (limit value 0,1 %)
- Cadmium (limit value 0,01 %)
- Hexavalent chromium (limit value 0,1 %)
- Polybrominated biphenyls (PBB) (limit value 0,1 %)
- Polybrominated diphenyl ethers (PBDE) (limit value 0,1 %)
- Bis(2-ethylhexyl) phthalate (DEHP) (limit value 0,1 %)
- Butyl benzyl phthalate (BBP) (limit value 0,1 %)
- Dibutyl phthalate (DBP) (limit value 0,1 %)
- Diisobutyl phthalate (DIBP) (limit value 0,1 %)

Version 4. The information contained herein is believed to be accurate as of the date of this document. If any of the above mentioned regulations change after the date of declaration, this information is no longer valid.

The manner in which you use our products, technical assistance and information (whether verbal, written or by way of production evaluations), including any suggested formulations and recommendations, are beyond our control. Therefore, it is imperative that you test our products to determine suitability for your processing and intended uses. Your analysis must at least include testing to determine suitability from a technical, health, safety, and environmental and regulatory standpoint. Such testing has not necessarily been done by _____ has not obtained any approvals or licenses for a particular use or application of the product, unless explicitly stated otherwise.

Unless we otherwise agree in writing, all products are sold strictly pursuant to the terms of our standard conditions of sale which are available upon request.

All information and including technical assistance is given without warranty or guarantee and is subject to change without notice. It is expressly understood and agreed by you that you assume and hereby expressly release indemnify us and hold us harmless from all liability, in tort, contract or otherwise, incurred in connection with the use of our products, technical assistance, and information. Any statement or recommendation not contained herein is unauthorized and shall not bind us. Nothing herein shall be construed as a recommendation to use any product in conflict with any claim of any patent relative to any material or its use. No license is implied or in fact granted under the claims of any patent.

This information is exclusively for our customers and respective competent authorities. It is not intended for reproduction either in printed or electronic form (e.g. via internet) by others. Thus, neither partial nor full reproduction is allowed without written permission from

Date: 2020-05-05