

HG-400 MiniG® Tissue Homogenizer and Cell Lyser

- Small footprint that minimizes bench space
- Vigorous clamp movement results in increased yields
- Consistent vertical motion of the clamp ensures equal conditions for all samples
- Kryo-Tech® accessories are available to preserve temperaturesensitive samples

The HG-400 MiniG is the ideal solution for labs that want a powerful tissue homogenizer and cell lyser. It is equipped with an adjustable clamp that accommodates a full range of sample vials from 2 mL to 50 mL centrifuge tubes or up to two deep-well titer plates. It is specifically designed for cell lysis and tissue homogenization through bead beating, enabling fast and efficient extraction of nucleic acids, proteins and other molecules of interest.

Features





Automated mechanical disruption through bead beating



Designed for vigorous up-and-down shaking



Easy data transfer



HG-400 MiniG®

Typical Applications Include

Tissue homogenization, DNA/RNA research and extraction, cell lysis, protein extraction, biofuel research, pesticide residue extraction using QuEChERS or the SweEt method.

Sample Types Include











Plant Tissue

Animal Tissue

Fruit

Cannabis

Yeast

Before & After Samples – Plant Tissue



Specifications

3.2 cm (1.25 in) vertical
Adjustable from 500 to 1500 strokes/minute
Digital display in minutes:seconds (max 10:00)
115 VAC, 60 Hz or 230 VAC, 50 Hz
Yes
1/7 HP
28.6 x 54.6 x 43.2 cm (11.3 x 21.5 x 17.0")
22 kg (49 lb)
3-prong grounded plug for 115 VAC or 2-prong grounded plug for 230 VAC
3 years

Ordering Information

Description	Item Number
HG-400 MiniG Tissue Homogenizer and Cell Lyser, 115/230 VAC, 50/60 Hz	04500-08

Need a Demo?

- Virtual sample processing virtual demonstration of the equipment and sample processing
- Physical sample processing physical testing of your sample with shared results
- Physical equipment testing a demo unit can be sent to your facility to test before purchasing

Contact us today at sampleprep@antylia.com for details.

cole-parmer.com

USA: +1.800.323.4340 +1.847.549.7600 Canada: +1.800.363.5900 China: +86.21.5109.9909 France: +33 (0) 1486 37800 Germany: +49 (0) 9377 92030 India: +1.800.266.1244 Italy: +39 (0) 2 84349215 UK: +44 (0) 1480.272279 All other countries: +1.847.549.7600

