




Masterflex® I/P® Pump Head Selection Guide

Description	Flow rates	Number of rollers	Multichannel or stackable	Special features
I/P Standard Pump Heads				
	0.01 to 13 LPM (0.002 to 3.5 GPM)	3	Yes, stack up to two pump heads	<ul style="list-style-type: none"> ✓ Low cost, high precision and accuracy ✓ Best choice for dispensing applications ✓ Each head dedicated to one tubing size
I/P Easy-Load® Pump Heads				
	0.01 to 13 LPM (0.002 to 3.5 GPM)	3	Yes, stack up to two pump heads	<ul style="list-style-type: none"> ✓ Quick tubing changes without dismounting pump head from drive ✓ Automatic tubing retention ✓ Model available for ATEX Zone 2 applications
I/P High-Performance Pump Heads				
	0.01 to 19 LPM (0.002 to 5.0 GPM)	3	No, single head only	<ul style="list-style-type: none"> ✓ Accepts High-Performance precision tubing sizes ✓ Highest flow rate, pressure and suction capabilities of any I/P® pump head ✓ Tubing enters and exits same side of pump head ✓ Model available for ATEX Zone 2 applications