

Biohazard Disposal Bags, HDPE

Hold more—up to 50 gallons

- Thick, 1.25-mil HDPE bags stand up to your needs
- No misinterpretations—procedures printed in four languages
- Know when it's autoclaved—indicator patch darkens for verification
- Autoclavable at 250°F (121°C)



Capacity	Size (W x L)		Catalog number	Qty/ cs	Price/ cs
	in.	cm			
2 to 4 gal.	14 x 19	35.6 x 48.3	GH-06494-00	200	
6 to 9 gal.	19 x 23	48.3 x 58.4	GH-06494-02		
10 to 12 gal.	25 x 35	63.5 x 88.9	GH-06494-04		
20 to 30 gal.	31 x 38	78.7 x 96.5	GH-06494-06		
40 to 50 gal.	38 x 48	96.5 x 121.9	GH-06494-08	100	

[GH-06831-15](#) Plastic ties, 4" L (10.2 cm). Pack of 1000

Autoclavable Biohazard Disposal Bags, HDPE

Meet or exceed
ASTM D 1709-85

- Thick, 1.25-mil HDPE construction
- No misinterpretations—procedures printed in four languages
- Know when it's autoclaved—indicator patch darkens for verification
- Autoclavable at 250°F (121°C)



Capacity	Size (W x L)		Catalog number	Qty/ pk	Price/ pk
	in.	cm			
½ to 1 gal.	12 x 24	30.5 x 61.0	GH-06497-30	100	
10 to 12 gal.	24 x 30	61.0 x 76.2	GH-06497-40	100	
15 to 20 gal.	24 x 36	61.0 x 91.4	GH-06497-50	100	

[GH-06497-14](#) Optional stand with tray; for bags up to 9 gal.


[GH-06497-18](#) Optional stand with tray; for bags 10 to 12 gal.

[GH-06831-15](#) Plastic twist ties, 4" L (10.2 cm). Pack of 1000

Scienceware® Sterile Scoop An' Bag, PS/PE

No need to buy a separate scoop and bag

- Sterilized and bagged together—lot-traceable packages
- Easy close twirl type closure
- FDA-compliant polystyrene scoop



Scoop capacity mL (oz)	Scoop handle	Bag size (W x L)	Catalog number	Qty/cs	Price/cs
60 (2)	4" (10.2 cm) L	4½" x 9" (11.4 x 22.9 cm)	GH-06260-15	50	

Desktop Biohazard Bag, HDPE

Goes where you need it

- Versatile bags can be used with optional stand or used to pick up individual items
- Know when it's autoclaved—indicator patch darkens for verification
- Autoclavable at 250°F (121°C)



Size (W x L)		Catalog number	Qty/ pk	Price/ pk	Optional stand	
in.	cm				Catalog number	Price
8½ x 11	21.6 x 27.9	GH-06496-50	100		GH-06496-60	

[GH-06831-15](#) Plastic twist ties, 4" L (10.2 cm). Pack of 1000

Heavy-Duty Biohazard Disposal Bags, PP

Don't worry about tears and leaks

- Stands up to your demands—extra strength 2-mil thick polypropylene
- No misinterpretations—procedures printed in four languages
- Know when it's autoclaved—indicator patch darkens for verification
- Autoclavable at 300°F (149°C)



Capacity	Size (W x L)		Catalog number	Qty/ pk	Price/ pk
	in.	cm			
2 to 4 gal.	14 x 19	35.6 x 48.3	GH-06495-00	200	
6 to 9 gal.	19 x 23	48.3 x 58.4	GH-06495-02	200	
10 to 12 gal.	25 x 35	63.5 x 88.9	GH-06495-04	200	

[GH-06497-14](#) Optional stand with tray; for bags up to 9 gal.

[GH-06497-18](#) Optional stand with tray; for bags 10 to 12 gal.

[GH-06831-15](#) Plastic twist ties, 4" L (10.2 cm). Pack of 1000