

Alcohol Lamp

Don't be tied to gas sources

- Durable, nickel-plated brass design
- Easily adjust height with two-way lamp stand

What's included:
snuffer cap, wick, and stand.



Dimensions (H x dia)	Catalog number	Price
3½" x 4" (9 x 10 cm)	GH-36300-20	

[GH-36300-26](#) Two-way lamp stand

[GH-36300-22](#) Replacement wicks. Pack of 12

Safety Spark Lighter

No fuel to change or store

- Just strike and light—it's that easy
- Durable hood construction protects flint

What's included: five flint renewals (order more separately below).



Description	Catalog number	Price
Safety spark lighter	GH-36136-50	

[GH-36136-55](#) Single flint renewals. Pack of 5

Test Tube Clamp

Safely handle samples while heating

- Sturdy gripping, spring-action jaws



Length	Material	Qty/pk	Catalog number	Price/pk
5" (12.7 cm)	Brass	5	GH-08048-60	

Wire Gauze

Won't fray!

- Stainless steel mesh withstands temperatures to 1472°F (800°C)
- Reinforced edges for durability



Dimensions (L x W)	Qty/pk	Catalog number	Price/pk
4" x 4" (10.2 x 10.2 cm)	10	GH-36300-40	
5" x 5" (12.7 x 12.7 cm)		GH-36300-42	
6" x 6" (15.2 x 15.2 cm)		GH-36300-44	

Portable Microburner

No need for gas lines

- No replacement wicks required—simple push-button ignition
- Won't tip over—sturdy, stable design with easy-grip handle
- Refill as needed with standard butane canister



Dimensions (W x H)	Catalog number	Price
5" x 3½" (13 x 9 cm)	GH-36310-47	

[GH-36310-50](#) Tripod microburner stand; 4½" (11.4 cm) height, 4½" (11.4 cm) ring OD, 3¼" (8.3 cm) ring ID

[GH-36138-90](#) Butane fuel canisters. Case of 12

Portable Torch Burner

Get more out of your burner

- Not just a torch—provided base easily converts torch to a burner
- No need for matches—simple, single-knob gas control with electronic auto ignition
- Refillable butane canister provides 1.5 hours of burn time up to 2500°F (1271°C)



What's included:
black base and metal stand.



Included metal stand converts torch to a benchtop burner.

Dimensions (L x W x H)	Catalog number	Price
5½" x 3½" x 8" (14 x 9 x 21 cm)	GH-36310-41	

[GH-36138-90](#) Butane fuel canisters. Case of 12

Wait!

There's More at ColeParmer.com

Find all the product specs you need!

Tripod Burner Stands

No need for ring clamps or stands

- Easily position over burners
- Made of cast iron top and steel legs, which are removable



Dimensions (H x dia)	Catalog number	Price
6" x 3" (15.2 x 7.6 cm)	GH-36300-46	
9" x 4" (22.9 x 10.2 cm)	GH-36300-49	