




KIMAX® Graduated Glass Cylinder Set

No need to order separate cylinders

- Get everything you need in one part number
- Get accurate measurements with calibration “to deliver”
- Contain one each of 10mL, 25mL, 50mL, 100mL, and 250mL sizes
- Guards included for 25 to 250mL cylinders



Description	Catalog number	Qty/pk	Price/pk
Graduated cylinder starter pack	GH-34547-20	5	

Cole-Parmer® Low-Form Graduated Glass Cylinders

Prevent accidental tipping

- Low profile design and wide base provide better stability
- Dual graduations for reading what's going in or out
- Calibrated “to deliver” for better accuracy and delivery
- Get better pouring with two spouts



Capacity (mL)	Graduations (mL)	Tolerance (mL)	Catalog number	Qty/pk	Price/pk
50	1	±1.5	GH-34300-35	1	
100	2	±1.0	GH-34300-36		

Thermo Scientific™ Nalgene™ Labware Value Pack

Everything you need to start your lab

- Won't break or shatter like glass
- Compatible with a wide range of chemicals
- Beakers meet ISO/DIN 7056 International Standards for Laboratory Plasticware Accuracy
- Graduated cylinders meet CFR 21, Part 177.1520, ASTM E 1272 Class B accuracy requirements and ISO Standard 6706
- Autoclavable (except unitary bottles); jar closure needs to be autoclaved separately

NEW



Contents	Material	Qty
Griffin low-form beakers: 50, 100, 250, 600, and 1000 mL	PPCO	5 (1 of ea size)
Graduated cylinders: 100 mL, 500 mL, and 1 L	PPCO	4 (2 x 100 mL, 1 x 500 mL, 1 x 1 L)
Unitary wash bottles: 500 mL	LDPE†	4
Straight-sided jars: 500 mL	PPCO	6
Unwire™ blue half-rack for 30-mm tubes	RMT	1

† LDPE wash bottles are not autoclavable.


Buy More...Save More!
20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Description	Catalog number	Price/pk
Labware value pack	GH-34500-90	

PYREX® Brand 3025 Graduated Glass Cylinders

No more calculating allocations

- Measure how much you pour in and out directly with double metric scale
- Calibrate “to contain”
- Autoclavable



Buy More...Save More!

15% off on 10+ packs or cases
10% off on 5 to 9 packs or cases

Capacity (mL)	Graduations (mL)	Catalog number	Price/pk of 1	Catalog number	Qty/cs	Price/cs
10	0.1	GH-34546-01		GH-34546-21	24	
25	0.2	GH-34546-02		GH-34546-22	18	
50	1.0	GH-34546-03		GH-34546-23	18	
100	1.0	GH-34546-04		GH-34546-24	12	
250	2.0	GH-34546-05		GH-34546-25	12	
500	5.0	GH-34546-06		GH-34546-26	8	
1000	10.0	—	—	GH-34546-27	1	
2000	20.0	—	—	GH-34546-28	1	