

Cole-Parmer® Cleaning Products

Easily clean glass, metal, plastic, rubber, and other hard materials

- Safe and effective cleaning products
- Highly concentrated, aqueous solutions are free-rinsing
- Meet USDA guidelines for incidental contact with food processing systems
- Do not contain CFCs, phosphates, silicates, halogens, or phenols



Cleaner	Type	Cleaning applications	Dilution	pH	Packaging	Cat. no.	Price/ea	Cat. no.	Qty/cs	Price/cs
Micro-90®	Ionic, nonionic, USDA authorized	Manual or ultrasonic; removes most biological materials; cleans glass, most metals, plastic, and rubber†	1:100 to 2:100	9.5	0.26 gal. (1 L)	GH-18100-05	—	GH-18100-04	12	—
					1 gal. (4 L)	—	GH-18100-11	4	—	
					5 gal. (18.9 L)	—	GH-18100-20	1	—	
					55-gal. drum (208 L)	GH-18100-30	—	—	—	
Zymit®	Enzymatic, USDA authorized	Machine, manual, or ultrasonic; dissolves protein and starch-based soils; may use for delicate materials	1:100	7.5	0.26 gal. (1 L)	GH-18101-30	—	GH-18101-20	12	—
LF2100™	Low-sudsing, anionic, nonionic, amphoteric, USDA authorized	Automatic washers, high-pressure and high agitation applications†	1:100	9.7	0.26 gal. (1 L)	GH-18102-00	—	GH-18102-10	12	—
					5.3 gal. (20 L)	GH-18102-30	—	—	—	
Surface-Cleanse/930®	Nonionic, USDA authorized	Cleans grease, petroleum, oils from glass, aluminum, lead, zinc, and plastic without surface damage	1:200	7.0	0.26 gal. (1 L)	GH-18103-00	—	GH-18103-10	12	—
					5.3 gal. (20 L)	GH-18103-30	—	—	—	
Micro-A07®	Citric acid, nonionic, USDA authorized	Removes millstone, hard water scale, rust, mineral deposits, and other inorganic soils from filter membranes, labware, and industrial equipment	1:100 to 2:100	2.5	0.26 gal. (1 L)	GH-18104-00	—	GH-18104-01	12	—
					5.3 gal. (20 L)	GH-18104-30	—	—	—	

†Do not use on zinc, magnesium, or aluminum.

DisCide® ULTRA Disinfecting Towelettes and Sprays

No wasting time—works in just one minute!

- No mixing or measuring—solutions are ready to use
- Eliminate separate towel requirements with towelettes



Description	Packaging	Qty/cs	Catalog number	Price
Towelettes, 6" x 6¾" (15.2 x 17.1 cm)	Canister of 160	12	GH-86306-03	—
Towelettes, 10½" x 10½" (26.7 x 26.7 cm)	Canister of 60	12	GH-86306-05	—
Spray bottle	1 quart bottle	12	GH-86306-13	—
Refill bottle	1 gallon bottle	4	GH-86306-15	—

Cole-Parmer® Clean-Wipes™

Won't scratch delicate surfaces

- No residual lint—made of strong, nonwoven cellulose and polyester
- No more struggling with solutions and separate towels—ready to use
- Individually sealed containers for use in cleanrooms

Choose wipes that are premoistened or dry. Convert dry wipes to moistened wipes by adding 8 oz of fluid to container.



Description	Wipe size	Packaging	Catalog number	Price
Premoistened with 70% isopropyl alcohol and 30% deionized water	6" x 9" (15.2 x 22.9 cm)	Canister of 100	GH-33675-03	—
Premoistened with 100% deionized water			GH-33675-05	—
Dry			GH-33675-07	—