

### Glove Bag™ Inflatable Glove Chambers

Don't risk product safety—  
or your own

- Effectively eliminate oxygen and moisture during material manipulation operations
- Establish high-purity working atmosphere in minutes
- Disposable chambers simplify cleanup



An alternative to standard glove boxes—these durable, polyethylene glove chambers are reusable, yet priced to be disposable. Chambers are easy to use—just slide your equipment through the sleeve(s), seal, connect the gas port (accepts 3/8" ID tubing) to your gas supply, and inflate. Models 04408-30, -32, -34, -36, and -38 have a single equipment sleeve and a gas port at the rear of the bag. Model 04408-40 has two equipment sleeves and two rear-mounted gas ports for added versatility.

**What's included:** one pair of cotton gloves, tubing coupler, and a closure. Order replacement cotton gloves below.

| Chamber dimensions (inflated) (L x W x H) | Width of equipment sleeve | Catalog number              | Price/ bx of 6 |
|---|---------------------------|-----------------------------|----------------|
| <b>Chambers with one equipment sleeve</b> |                           |                             |                |
| 17" x 17" x 11" (43.2 x 43.2 x 27.9 cm)   | 11½" (29.2 cm)            | <a href="#">GH-04408-30</a> |                |
| 17" x 27" x 12" (43.2 x 68.6 x 30.5 cm)   | 22" (55.9 cm)             | <a href="#">GH-04408-32</a> |                |
| 27" x 27" x 15" (68.6 x 68.6 x 38.1 cm)   | 22½" (57.2 cm)            | <a href="#">GH-04408-34</a> |                |
| 27" x 37" x 18" (68.6 x 94.0 x 45.7 cm)   | 33½" (85.1 cm)            | <a href="#">GH-04408-36</a> |                |
| 37" x 37" x 25" (94.0 x 94.0 x 63.5 cm)   | 34½" (87.6 cm)            | <a href="#">GH-04408-38</a> |                |
| <b>Chamber with two equipment sleeves</b> |                           |                             |                |
| 20" x 20" x 12" (50.8 x 50.8 x 30.5 cm)   | 12" (30.5 cm)             | <a href="#">GH-04408-40</a> |                |

[GH-04408-50](#) Replacement gloves, cotton. Box contains 12 pairs

### Captair® Pyramid Glove Bag

Set up controlled environments anywhere

- Protects you from hazardous materials
- Saves lab space
- Assembles in minutes



Unit features an 18½" (47 cm) side opening for introduction of materials, a zip lock to ensure airtight sealing, and a port to exhaust/purge gas. Pyramid is constructed from transparent, 250 µm PVC; with frame and 0.2-mm thick butyl gloves.

**What's included:** 1/8" ID coupler body valved fitting.

| Chamber dimensions (W x H x D)           | Width of opening | Catalog number              | Price |
|--|------------------|-----------------------------|-------|
| 30" x 28½" x 22" (76.2 x 72.4 x 55.9 cm) | 18½" (47 cm)     | <a href="#">GH-33666-50</a> |       |

### Cole-Parmer® Glove Boxes

Monitor humidity and protect materials—affordably!

- Slanted window eliminates optical distortion
- Spatially efficient with ample working chamber

Use these economical glove boxes on your crowded lab bench or in large walk-in areas. The wide front access door makes loading equipment easy. Clear 1/4"-thick acrylic access and pass box doors ensure good visibility. Painted steel construction endures everyday use. The included chamber hygrometer monitors humidity from 20 to 95% RH. Two ball valves are for purging gas.

**What's included:** hygrometer, two ball valves, and one pair of medium-sized latex gloves.

#### Specifications

**Pass box dimensions (W x H x D):** 8¾" x 8¼" x 8¼" (21.3 x 21.0 x 21.0 cm)      **Glove size:** 6" (15.2 cm) dia cuffs x 24" (61.0 cm) L  
**Glove ports:** 6" (15.2 cm) dia O-rings      **Valve size:** ¼" OD

| Dimensions                              |                            | Shpg wt lb (kg) | Catalog number              | Price |
|---|----------------------------|-----------------|-----------------------------|-------|
| Chamber (W x H x D)                     | Access opening (W x H)     |                 |                             |       |
| 27" x 20" x 20" (68.6 x 50.8 x 50.8 cm) | 27" x 17" (68.6 x 43.2 cm) | 65 (29.5)       | <a href="#">GH-34788-00</a> |       |
| 32" x 20" x 24" (81.3 x 50.8 x 61.0 cm) | 32" x 20" (81.3 x 50.8 cm) | 85 (38.6)       | <a href="#">GH-34788-10</a> |       |



Cole-Parmer®

#### Accessories

- [GH-37802-00](#) Replacement hygrometer
- [GH-34790-80](#) Replacement latex gloves, medium size. Measure 24" (61.0 cm) long with 6" (15.2 cm) cuffs