

Hamilton Scientific Laboratory Workbench Assemblies

Easy ordering—one part number, a complete system!

- Durable construction—made of epoxy-coated painted steel and 1" thick epoxy work surfaces
- Require installation, not included
- Choose your color choice from chart at right

Sitting-Height Wall Assemblies

- Plenty of storage with three cabinets and drawers
- Don't let stools get in your way—features areas for two lab stools



Description	Dimensions (W x H x D)		Shpg wt		Catalog number	Price
	in.	cm	lb	kg		
8½-ft (2.6-m) three-cabinet assembly with sitting areas	102 x 30¾ x 30	259 x 77 x 76	631	286	GH-41524-00	
10-ft (3-m) three-cabinet assembly with sitting areas	120 x 30¾ x 30	305 x 77 x 76	822	373	GH-41524-05	

Standing-Height Wall Assemblies with Fume Hood

- Handle hazardous materials safely with 48" wide hood—includes four service fixtures and cup sink
- Includes four cabinets, sink, and black epoxy resin top
- Don't forget ductwork and blower for fumehood (sold separately)



Description	Dimensions (W x H x D)		Shpg wt		Catalog number	Price
	in.	cm	lb	kg		
14-ft (4.2-m) four-cabinet assembly with fume hood	168 x 36¼ x 30	427 x 92 x 76	1656	751	GH-41524-55	
16-ft (4.9-m) four-cabinet assembly with fume hood	192 x 36¼ x 30	488 x 92 x 76	1752	795	GH-41524-65	

Standing-Height Wall Assemblies with Sink

- Maximize bench space and storage with four cabinets
- Includes sink, faucet, and epoxy resin top



Dimensions (W x H x D)		Shpg wt		Catalog number	Price
in.	cm	lb	kg		
144 x 36¼ x 30	366 x 92 x 76	1026	465	GH-41524-70	
168 x 36¼ x 30	427 x 92 x 76	1127	511	GH-41524-75	

Sink Cabinet Assemblies

- Place just about anywhere in your facility
- Includes sink, faucet, and epoxy resin top



Dimensions (W x H x D)		Shpg wt		Catalog number	Price
in.	cm	lb	kg		
36 x 36¼ x 30	91 x 92 x 76	283	128	GH-41524-80	
48 x 36¼ x 30	122 x 92 x 76	305	138	GH-41524-85	

Customize your selection

Select your color at time of order

	Petal White - PW
	Shell White - SW
	Chameleon - CH
	Platinum - PL
	Sand - SA
	Sandstone - SS
	Dove Gray - G1
	Gray Slate - G3
	Khaki - KK
	Dark Khaki - DK
	Piedmont Green - PM
	Hunter Green - HG
	Blue Slate - BS
	Blue - BL
	Indigo - IN
	Purple - PA
	Brown Burgundy - BD
	Black - BK