

Thermo Scientific™ Nalgene™ UV-Protective Wraparound Face Shield

Don't lose your breath

- Full-length, wrap-around shield sits away from face for easy breathing

Optically clear window of 0.06" thick polycarbonate protects against UV radiation from 200 to 360 nm. Adjustable headband.

Compliance: ANSI Z87.1, 29 CFR Part 1910.1030



Description	Catalog number	Price
UV-Protective wraparound face shield	GH-06767-00	

MonoShield® Face Shield

No need for separate goggles and shield

Shield provides both primary and secondary eye protection. Attached MonoGoggle® goggles feature a soft pliable nose piece and flexible frame for a snug, comfortable fit. Lens gives you distortion-free vision. Clear polycarbonate shield protects your face. Shield features FogGard® Plus antifog coating.

Compliance: ANSI Z87.1+ (High impact), CSA Z94.3, SEI certified



Description	Lens	Catalog number	Price each	
			1 ea	10 ea
MonoShield shield	Clear, antifog	GH-81657-30		

Uvex® by Honeywell Bionic® Face Shields

Protect you from head to chin

Shield provides secondary protection for workers exposed to falling or flying objects, impact, chemical splash, and airborne debris. Lightweight design, foam backing, and customizable fit make this face shield ideal for extended use. Fits comfortably over most goggles and respirators.

Compliance: ANSI Z87-1.2003, CSA Z94.3



Material	Catalog number	Price per each	
		1 ea	10 ea
Head gear with face shield			
PC, uncoated	GH-81690-11		
PC, antifog/hard coat	GH-81690-12		
Replacement face shields			
PC, uncoated	GH-81690-13		
PC, antifog/hard coat	GH-81690-14		

Sellstrom® Acetate Face Shield Provides chemical protection at a great price

Ratcheting head gear allows for fast and easy adjustment. Face shield curves naturally to fit facial contours ensuring reliable protection from splash, particles, and flying debris. Acetate window is impact and chemical splash resistant. Window easily attaches with keyhole design and locks in the up or down position depending on need. Nonglare finish allows for high clarity.



Compliance: ANSI Z87.1+ (High impact), CUL, CAN/CSA-Z94.3 Standards

Lens	Catalog number	Price
Headgear with face shield		
Clear	GH-86478-16	
Clear, antifog	GH-86478-17	
Replacement face shield		
Clear	GH-86478-18	
Clear, antifog	GH-86478-19	

North® by Honeywell Protecto-Shield® Face Shields

Protect yourself against liquid splashes, sparks, and impacts

- Adjustable ratchet suspension and tension knob for precise sizing and visor positioning
- Splash drip edge redirects splashing or spraying fluids away from you



Head gear 81690-00 with shield 81690-20

Lightweight construction provides comfort during lengthy work periods. Shields attach easily and securely to head gear—no snaps, posts, or levers. Sweatband absorbs perspiration. Can be used with earmuffs.

See comparison table below to determine which material (propionate or polycarbonate) is appropriate for your application.

Compliance: ANSI Z87-1.2010, CSA Z94.3

Material	Catalog number	Price	
		1 ea	10 ea
Head gear			
HDPE	GH-81690-00		
Face shields			
Propionate	GH-81690-10		
PC	GH-81690-20		

Comparison of Materials

Resistance	Propionate	PC
Impact	Good	Excellent
Water	Good	Excellent
Weather	Fair	Good
Scratch	Good	Fair
Acid	Fair	Good
Alkaline	Fair	Good
Solvent	Poor	Good
Heat	220°F	280°F