

Oakton® Electrode Cleaning and Storage Solutions

Clean electrodes make clean measurements

- Easily remove grease, protein, and other deposits with cleaning solution
- Make electrode last longer—store in our storage solution
- Choose 500-mL bottle or case of 24 500-mL bottles



Solution type	Catalog number	Price/ea	Catalog number	Price/cs
Cleaning	GH-00653-06		GH-35655-06	
Storage	GH-00653-04		GH-35655-04	

Oakton® Reference Fill Solutions

Effortless refilling!

- Choose your solution: 3.8 KCl with AgCl for Ag/AgCl electrodes or 4 KCl for calomel
- Sold in packs of two 125-mL bottles



Description	Catalog number	Price/pk
3.8 KCl with AgCl	GH-05992-47	
4 KCl	GH-05992-48	

Thermo Scientific™ Orion™ ROSS™ Electrode Storage Solution

Optimize your ROSS electrode performance

- Specially formulated for ROSS pH electrodes
- 475-mL bottle



Description	Catalog number	Price
ROSS pH electrode storage solution	GH-05730-60	

Oakton® Grip-Clip™ Holder

Hands-free measurements **NEW**

- No messing with electrode holders—simply clip to side of beaker for easier probe handling
- Holds an ATC probe and a 11- or 12-mm probe or a 16-mm probe



Description	Catalog number	Price
Oakton Grip-Clip holder	GH-35614-50	

Thermo Scientific™ Orion™ pH Electrode Cleaning Kit

Get longer electrode life

NEW

- Restores performance of your electrode
- Remove protein, bacteria, oil, and grease with ease
- Includes one bottle each of cleaning solution, beaker, and pipette



Description	Catalog number	Price
pH electrode cleaning kit	GH-05730-70	

Accessories

GH-05730-71 Replacement solution A for removal of proteins. Four 30-mL bottles, beaker, and pipette

GH-05730-72 Replacement solution B for removal of bacteria. Four 60-mL bottles, beaker, and pipette

GH-05730-73 Replacement solution C for general-purpose cleaning. Four 30-mL bottles, beaker, and pipette

GH-05730-74 Replacement solution D for removal of oil and grease. Four 60-mL bottles, beaker, and pipette

Electrode Saver Bottles

Keeps electrodes in working order

- Protect against bumps, spills, and drying out
- Accepts electrodes up to 13 mm diameter



Capacity (mL)	Dimensions (H x dia)	Catalog number	Price
50	4" x 1½" (10 x 3.8 cm)	GH-05990-99	
5	1¾" x 7/8" (4.4 x 2.2 cm)	GH-35805-50	

Electrode Storage Sleeve

Eliminate broken pH bulbs

- Protect fragile pH glass bulbs up to 12-mm dia
- Keep electrodes conditioned and ready for pH measurement
- Weighted base for safe, upright storage

NEW



Description	Catalog number	Price
Electrode storage sleeve	GH-99570-50	

Find even more online! Go to ColeParmer.com to search more than 100,000 products.