

### WHEATON® Economical Sample Glass Vials

Don't worry about contaminants—shrink wrapped to keep vials clean



Clear sample glass vials



Amber sample glass vials

- Tight-fitting screw caps for no leaks
- Made of 33 low-extractable borosilicate glass
- Protect light-sensitive samples with amber-colored vials
- Choose the cap that's right for your sample
- Autoclavable

Color	Capacity	Cap size	Catalog number	Qty/cs	Price/cs
<b>Vials with rubber-lined phenolic threaded cap</b>					
Clear	2 mL	8-425	<a href="#">GH-08923-10</a>	200	
	4 mL	13-425	<a href="#">GH-08923-11</a>		
	8 mL	15-425	<a href="#">GH-08923-12</a>		
Clear	12 mL	15-425	<a href="#">GH-08923-13</a>	200	
	16 mL	18-400	<a href="#">GH-08923-14</a>		
	24 mL	20-400	<a href="#">GH-08923-15</a>		
	2 mL	8-425	<a href="#">GH-08923-16</a>		
Amber	4 mL	13-425	<a href="#">GH-08923-17</a>	200	
	8 mL	15-425	<a href="#">GH-08923-18</a>		
<b>Vials with PTFE/rubber-lined threaded cap</b>					
Clear	2 mL	8-425	<a href="#">GH-08923-20</a>	200	
	4 mL	13-425	<a href="#">GH-08923-21</a>		
	8 mL	15-425	<a href="#">GH-08923-22</a>		
	12 mL	15-425	<a href="#">GH-08923-23</a>		
Clear	16 mL	18-400	<a href="#">GH-08923-24</a>	200	
	24 mL	20-400	<a href="#">GH-08923-25</a>		
	2 mL	8-425	<a href="#">GH-08923-26</a>		
	4 mL	13-425	<a href="#">GH-08923-27</a>		
Amber	8 mL	15-425	<a href="#">GH-08923-28</a>	200	
<b>Vials with no cap</b>					
Clear	2 mL	8-425	<a href="#">GH-08923-30</a>	200	
	4 mL	13-425	<a href="#">GH-08923-31</a>		
	8 mL	15-425	<a href="#">GH-08923-32</a>		
	12 mL	15-425	<a href="#">GH-08923-33</a>		
Clear	16 mL	18-400	<a href="#">GH-08923-34</a>	200	
	24 mL	20-400	<a href="#">GH-08923-35</a>		
	2 mL	8-425	<a href="#">GH-08923-36</a>		
	4 mL	13-425	<a href="#">GH-08923-37</a>		
Amber	8 mL	15-425	<a href="#">GH-08923-38</a>	200	

**Wait!**

**There's More at  
ColeParmer.com**

Find more than **100,000**  
products to choose from!

### WHEATON® Scintillation Vials, Glass

Stand up to most chemicals

- Sample and store up to 20 mL
- Measure 2<sup>3</sup>/<sub>8</sub>" H x 1<sup>1</sup>/<sub>8</sub>" OD (61 mm H x 28 mm OD) with cap



Cap material	Cap liner	Cap size	Caps	Catalog number	Qty/cs	Price/cs
Urea	Metal foil	22	On	<a href="#">GH-08918-01</a>	500	
Urea	Polyseal™ cone			<a href="#">GH-08918-02</a>		
Urea	Polyethylene disc			<a href="#">GH-08918-03</a>		
Urea	Polyethylene disc	24	On	<a href="#">GH-08918-05</a>	500	
Polypropylene	Metal foil	22		<a href="#">GH-08918-06</a>		

### WHEATON® Scintillation Vials, PE

Economically sample and store products

- Sample and store up to 20 mL
- Order with caps on or bulk packed separately
- Lightweight and durable vials measure 2<sup>3</sup>/<sub>8</sub>" H x 1<sup>1</sup>/<sub>8</sub>" OD (61 mm H x 27 mm OD) with cap



Cap material	Cap liner	Cap size	Caps	Catalog number	Qty/pk	Price/pk
Urea	Metal foil	22	On	<a href="#">GH-08918-51</a>	500	
Polyethylene	Linerless			<a href="#">GH-08918-52</a>		
Polypropylene	Metal foil			<a href="#">GH-08918-54</a>		
Polyethylene	Linerless	22	Bulk	<a href="#">GH-08918-62</a>	1000	
Polypropylene	Metal foil			<a href="#">GH-08918-53</a>		

### Snap-Seal™ Sample Containers

Won't spill or leak

- Cap remains securely locked
- Reduce chance of contamination with hinged-cap design
- Autoclavable



Capacity	Catalog number	Qty/pk	Price/pk
13 mL	<a href="#">GH-62261-00</a>	500	
45 mL	<a href="#">GH-62261-10</a>	400	
120 mL	<a href="#">GH-62261-20</a>	200	
240 mL	<a href="#">GH-62261-30</a>	100	
300 mL	<a href="#">GH-62261-40</a>	100	