

Crystallizing Dishes, Glass

Reduced chipping—reinforced and fire-polished rims

- Withstand repeated sterilizations—wet or dry
- Autoclavable



Capacity (oz)	Approx dia x H (mm)	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/pk	Price/cs
180 (6)	70 x 50	GY-34550-01	6		GY-34550-21	24	
180 (6)	80 x 40	GY-34550-02	6		GY-34550-22	24	
270 (9)	90 x 50	GY-34550-03	6		GY-34550-23	18	
325 (11)	100 x 50	GY-34550-04	6		GY-34550-24	18	
740 (25)	125 x 65	GY-34550-05	4		GY-34550-25	12	
1200 (30)	150 x 75	GY-34550-06	4		GY-34550-26	8	
1770 (60)	170 x 90	GY-34550-07	2		GY-34550-27	8	
2500 (85)	190 x 100	GY-34550-08	2		GY-34550-28	6	

Standard-Form Evaporating Dishes, Porcelain

Clean up easier with glazed interior

- Easy-pour spout
- Autoclavable



Capacity (mL)	Top outside dia (mm)	Height (mm)	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/cs	Price/cs
35	60	24	GY-17812-00	12		GY-17812-20	48	
70	75	30	GY-17812-02	12		GY-17812-22	48	
80	80	30	GY-17812-04	6		GY-17812-24	24	
120	94	42	GY-17812-06	6		GY-17812-26	24	
150	100	42	GY-17812-07	6		GY-17812-27	18	
250	115	45	GY-17812-08	6		GY-17812-28	18	
385	145	48	GY-17812-09	1		GY-17812-29	12	
525	162	51	GY-17812-10	1		GY-17812-30	12	
765	185	54	GY-17812-12	1		GY-17812-32	8	
1285	215	75	GY-17812-14	1		GY-17812-34	6	
2100	265	80	GY-17812-16	1		GY-17812-36	4	
3250	305	95	GY-17812-18	1		GY-17812-38	3	

Evaporating Dishes, Glass

Reusable dishes save you money

- Flat-bottom evaporating dishes with a lip and spout and rugged beaded rims
- Autoclavable



Capacity (mL)	Top outside dia (mm)	Height (mm)	Catalog number	Price/pk	Catalog number	Qty/cs	Price/cs
140	80	45	—	—	GY-34586-20	6	
170	90	50	—	—	GY-34586-22	6	
290	105	55	GY-34586-04		GY-34586-24	6	

Shallow-Form Evaporating Dishes, Porcelain

Easy pouring spout for less mess

- Glazed interior and partial exterior
- Autoclavable



Capacity (mL)	Top outside dia (mm)	Height (mm)	Catalog number	Qty/pk	Price/pk	Catalog number	Qty/cs	Price/cs
30	70	16	GY-17814-00	6		GY-17814-20	24	
50	80	20	GY-17814-02	6		GY-17814-22	24	
75	90	22	GY-17814-04	1		GY-17814-24	18	
100	105	23	GY-17814-06	1		GY-17814-26	18	
195	120	34	GY-17814-08	1		GY-17814-28	12	
290	160	31	GY-17814-10	1		GY-17814-30	8	

Petri Dish Racks

Organize your dishes to save valuable bench space

- Easy viewing of incubating petri dishes
- Use with plastic dishes only

Capacity	Dimensions (L x W x H)	Cat. no.	Price/ea
56 dishes, 60 mm dia	10½" x 6½" x 5½" 267 x 165 x 140 mm	GY-06146-00	
24 dishes, 100 mm dia	8½" x 4" x 8" 206 x 102 x 203 mm	GY-06146-10	
60 dishes, 100 mm dia	13" x 7¾" x 7¾" 330 x 200 x 197 mm	GY-06146-30	

