




Barbed Fittings (continued)

Barbed fittings are designed for quick and easy assembly without tools. Combine these simple, economical fittings with our flexible tubing for use in your low-pressure applications (generally less than 30 psi). Order tubing on pages 988–1017.


For material descriptions, refer to page 302.

Single barb fittings seal better than multi-barb fittings because they allow the tubing to relax around the barb.

NPT male branch tees



NPT female threaded adapters



Press-in plugs



Tubing ID	Material	Key	Catalog number	Qty/ pk	Price/ pk
NPT male branch tees, NPT(M) branch x tubing ID					
1/16" x 1/8"	316 SS	BS	GY-31209-13	1	
1/16" x 3/16"	316 SS	BS	GY-31209-14	1	
1/8" x 1/16"	316 SS	BS	GY-31209-15	1	
1/8" x 3/32"	316 SS	BS	GY-31209-16	1	
1/8" x 1/8"	316 SS	BS	GY-31209-17	1	
1/8" x 3/16"	316 SS	BS	GY-31209-18	1	
1/8" x 1/4"	HDPE	BO	GY-31701-86	10	
1/8" x 1/4"	Nylon	BP	GY-40610-72	10	
1/8" x 1/4"	PP	BQ	GY-40610-72	10	
1/8" x 1/4"	PVDF	BR	GY-30704-61	10	
1/8" x 1/4"	316 SS	BS	GY-31209-19	1	
1/8" x 3/8"	PP	BQ	GY-40610-73	10	
1/8" x 3/8"	PVDF	BR	GY-30704-62	10	
1/8" x 3/8"	316 SS	BS	GY-31209-20	1	
1/4" x 1/16"	316 SS	BS	GY-31209-21	1	
1/4" x 1/8"	316 SS	BS	GY-31209-23	1	
1/4" x 3/16"	316 SS	BS	GY-31209-24	1	
1/8" x 5/32"	HDPE	BO	GY-30623-96	10	
1/8" x 5/32"	Nylon	BP	GY-30623-98	10	
1/8" x 5/32"	PP	BQ	GY-40623-99	10	
1/8" x 5/32"	PVDF	BR	GY-30623-97	10	
1/8" x 3/8"	HDPE	BO	GY-30624-00	10	
1/8" x 3/8"	Nylon	BP	GY-30624-02	10	
1/4" x 1/4"	HDPE	BO	GY-30624-04	10	
1/4" x 1/4"	Nylon	BP	GY-30624-05	10	
1/4" x 1/4"	PP	BQ	GY-40610-74	10	
1/4" x 1/4"	PVDF	BR	GY-30704-63	10	
1/4" x 3/8"	HDPE	BO	GY-30624-06	10	
1/4" x 3/8"	Nylon	BP	GY-30624-07	10	
1/4" x 3/8"	PP	BQ	GY-40624-09	10	
1/4" x 3/8"	PVDF	BR	GY-30704-64	10	
1/4" x 1/2"	HDPE	BO	GY-30624-10	10	
1/4" x 1/2"	Nylon	BP	GY-30624-11	10	
1/4" x 1/2"	PP	BQ	GY-40610-76	10	
1/4" x 1/2"	PVDF	BR	GY-30704-65	10	
3/8" x 3/16"	316 SS	BS	GY-31209-28	1	
3/8" x 1/4"	HDPE	BO	GY-30624-12	10	
3/8" x 1/4"	Nylon	BP	GY-30624-13	10	
3/8" x 1/4"	PP	BQ	GY-40610-77	10	
3/8" x 1/4"	PVDF	BR	GY-30704-66	10	
3/8" x 1/4"	316 SS	BS	GY-31209-29	1	
3/8" x 3/8"	HDPE	BO	GY-30624-14	10	
3/8" x 3/8"	Nylon	BP	GY-30624-15	10	
3/8" x 3/8"	PP	BQ	GY-40610-78	10	
3/8" x 3/8"	PVDF	BR	GY-30704-67	10	
3/8" x 3/8"	316 SS	BS	GY-31209-30	1	
3/8" x 1/2"	HDPE	BO	GY-30624-16	10	
3/8" x 1/2"	Nylon	BP	GY-30624-17	10	
3/8" x 1/2"	PP	BQ	GY-40610-79	10	
3/8" x 1/2"	PVDF	BR	GY-30704-68	10	
1/2" x 1/4"	HDPE	BO	GY-30624-20	10	
1/2" x 1/4"	Nylon	BP	GY-30624-21	10	
1/2" x 1/4"	PP	BQ	GY-40610-80	10	
1/2" x 1/4"	PVDF	BR	GY-30704-69	10	
1/2" x 3/8"	HDPE	BO	GY-30624-22	10	
1/2" x 3/8"	Nylon	BP	GY-30624-23	10	
1/2" x 3/8"	PP	BQ	GY-40610-81	10	
1/2" x 3/8"	PVDF	BR	GY-30704-70	10	
1/2" x 1/2"	HDPE	BO	GY-30624-24	10	
1/2" x 1/2"	Nylon	BP	GY-30624-25	10	
1/2" x 1/2"	PP	BQ	GY-40610-82	10	
1/2" x 1/2"	PVDF	BR	GY-30704-71	10	

Tubing ID	Material	Key	Catalog number	Qty/ pk	Price/ pk
NPT male branch tees, NPT(M) branch x tubing ID—cont.					
1/2" x 3/4"	HDPE	BO	GY-30624-18	10	
1/2" x 3/4"	Nylon	BP	GY-30624-19	10	
1/2" x 3/4"	PP	BQ	GY-40610-83	10	
1/2" x 3/4"	PVDF	BR	GY-30704-72	10	
3/4" x 1/4"	HDPE	BO	GY-30623-86	10	
3/4" x 1/4"	Nylon	BP	GY-30623-87	10	
3/4" x 1/4"	PP	BQ	GY-40610-84	5	
3/4" x 1/4"	PVDF	BR	GY-30704-73	5	
3/4" x 3/8"	HDPE	BO	GY-30623-88	10	
3/4" x 3/8"	Nylon	BP	GY-30623-90	10	
3/4" x 3/8"	PP	BQ	GY-40610-85	5	
3/4" x 3/8"	PVDF	BR	GY-30623-89	5	
3/4" x 1/2"	HDPE	BO	GY-30623-91	10	
3/4" x 1/2"	Nylon	BP	GY-30623-93	10	
3/4" x 1/2"	PP	BQ	GY-40610-86	5	
3/4" x 1/2"	PVDF	BR	GY-30704-75	5	
3/4" x 3/4"	HDPE	BO	GY-30401-71	10	
3/4" x 3/4"	PP	BQ	GY-40610-87	5	
3/4" x 3/4"	HDPE	BO	GY-30623-81	5	
3/4" x 3/4"	Nylon	BP	GY-30623-82	5	
3/4" x 3/4"	PP	BQ	GY-40623-83	10	
3/4" x 3/4"	PVDF	BR	GY-30704-76	5	
3/4" x 1"	HDPE	BO	GY-30623-84	5	
3/4" x 1"	Nylon	BP	GY-30623-85	5	
3/4" x 1"	PP	BQ	GY-40610-88	5	
3/4" x 1"	PVDF	BR	GY-30704-77	5	
1" x 1"	HDPE	BO	GY-30623-94	5	
1" x 1"	Nylon	BP	GY-30623-95	5	
1" x 1"	PP	BQ	GY-40610-89	5	
1" x 1"	PVDF	BR	GY-30704-78	5	
NPT female threaded adapters, NPT(F) x tubing ID					
1/8" x 1/8"	Nylon	BT	GY-31500-40	25	
1/8" x 1/8"	Clear PP	BU	GY-31501-40	25	
1/4" x 1/8"	Nylon	BT	GY-31500-41	25	
1/4" x 1/8"	Clear PP	BU	GY-31501-41	25	
1/4" x 1/4"	Nylon	BT	GY-31702-20	10	
1/4" x 3/8"	Nylon	BT	GY-31702-22	10	
Press-in plugs					
1/16"	Nylon	BW	GY-31220-11	10	
1/16"	PP	BX	GY-31220-01	10	
1/16"	PVDF	BY	GY-31220-21	10	
3/32"	Nylon	BW	GY-31220-12	10	
3/32"	PP	BX	GY-31220-02	10	
3/32"	PVDF	BY	GY-31220-22	10	
1/8"	Nylon	BW	GY-31220-13	10	
1/8"	PP	BX	GY-31220-03	10	
1/8"	PVDF	BY	GY-31220-23	10	
5/32"	Nylon	BW	GY-31220-14	10	
5/32"	PP	BX	GY-31220-04	10	
5/32"	PVDF	BY	GY-31220-24	10	
3/16"	Nylon	BW	GY-31220-15	10	
3/16"	PP	BX	GY-31220-05	10	
3/16"	PVDF	BY	GY-31220-25	10	
1/4"	Nylon	BW	GY-31220-16	10	
1/4"	PP	BX	GY-31220-06	10	
1/4"	PVDF	BY	GY-31220-26	10	