

## Zip-Lip Bags, LDPE

### Won't let in contaminants

- No need to worry about dust or moisture getting to your dry samples
- Single track seal not for use with liquids
- Easily identify samples by using bags with write-on labels
- FDA-compliant



Size (W x L)		Thickness (mil)	Catalog number	Qty/ pk	Price/ pk
in.	cm				
<b>Zip-lip bags without labeling area</b>					
2 x 3	5.1 x 7.6	2	<a href="#">GY-60101-00</a>	1000	
3 x 5	7.6 x 12.7		<a href="#">GY-60101-10</a>		
4 x 4	10.2 x 10.2		<a href="#">GY-60101-20</a>		
4 x 6	10.2 x 15.2	2	<a href="#">GY-60101-30</a>	1000	
5 x 8	12.7 x 20.3		<a href="#">GY-60101-40</a>		
6 x 6	15.2 x 15.2		<a href="#">GY-60101-50</a>		
6 x 9	15.2 x 22.9	4	<a href="#">GY-60101-60</a>	1000	
8 x 10	20.3 x 25.4	2	<a href="#">GY-60101-70</a>		
9 x 12	22.9 x 30.5	3	<a href="#">GY-60101-80</a>		
12 x 15	30.5 x 38.1	2	<a href="#">GY-60101-90</a>		
<b>Zip-lip bags with labeling area</b>					
2 x 3	5.1 x 7.6	2	<a href="#">GY-60102-00</a>	1000	
3 x 5	7.6 x 12.7		<a href="#">GY-60102-10</a>		
4 x 6	10.2 x 15.2		<a href="#">GY-60102-30</a>		
5 x 8	12.7 x 20.3	2	<a href="#">GY-60102-40</a>	1000	
6 x 9	15.2 x 22.9		<a href="#">GY-60102-60</a>		
<b>Assortment pack, zip-lip bags w/o label area; 100 ea. of 60101-10, -40, -50, -60, &amp; -80</b>					
—	—	—	<a href="#">GY-06503-90</a>	500	

## Heavy-Duty Bag, PE

### No more weak bags

- Conforms to ordinances for disposal of dead animals
- Ideal for animal research labs, and humane societies




Size (W x L)		Thickness (mil)	Catalog number	Qty/ pk	Price/ pk
in.	cm				
36 x 50	91.4 x 127	4	<a href="#">GY-06504-10</a>	25	

## Autoclavable Bags, PP

### No worrying about contaminants

- Stands up to your demands—sturdy 1.5-mil polypropylene construction.
- Autoclavable at 250°F (121°C)



Size (W x L)		Thickness (mil)	Catalog number	Qty/ pk	Price/ pk
in.	cm				
4 x 6	10.2 x 15.2	1.5	<a href="#">GY-06505-01</a>	100	
4 x 10	10.2 x 25.4	1.5	<a href="#">GY-06505-03</a>	100	
6 x 10	15.2 x 25.4	1.5	<a href="#">GY-06505-05</a>	100	
6 x 12	15.2 x 30.5	1.5	<a href="#">GY-06505-07</a>	100	
10 x 16	25.4 x 40.6	1.5	<a href="#">GY-06505-09</a>	100	
12 x 18	30.5 x 45.7	1.5	<a href="#">GY-06505-11</a>	100	
12 x 24	30.5 x 70	1.5	<a href="#">GY-06505-13</a>	100	
16 x 18	40.6 x 45.7	1.5	<a href="#">GY-06505-15</a>	100	
18 x 23	45.7 x 58.2	1.5	<a href="#">GY-06505-17</a>	100	
22 x 30	55.9 x 76.2	1.5	<a href="#">GY-06505-19</a>	100	

[GY-06831-15](#) Plastic twist ties, 4"L (10.2 cm). Pack of 1000

## Bags, LDPE

### Stands up to your needs with strong bottom seal

- Seal with portable heat sealer or bag ties



Portable heat sealer 03014-00

Size (W x L)		Thickness (mil)	Catalog number	Qty/ pk	Price/ pk
in.	cm				
3 x 5	7.6 x 12.7	2	<a href="#">GY-06505-02</a>	1000	
3 x 8	7.6 x 20.3		<a href="#">GY-06505-04</a>		
4 x 5	10.2 x 12.7		<a href="#">GY-06505-06</a>		
5 x 7	12.7 x 17.8		<a href="#">GY-06505-08</a>		
6 x 9	15.2 x 22.9	2.5	<a href="#">GY-06505-10</a>	500	
6 x 18	15.2 x 45.7	3	<a href="#">GY-06505-12</a>	500	
8 x 10	20.3 x 25.4		<a href="#">GY-06505-14</a>		
10 x 12	25.4 x 30.5		<a href="#">GY-06505-16</a>		
12 x 18	30.5 x 45.7	2	<a href="#">GY-06505-18</a>	500	
18 x 24	45.7 x 61		<a href="#">GY-06505-20</a>		
18 x 30	45.7 x 76.2		<a href="#">GY-06505-22</a>		

[GY-03014-00](#) Portable heat sealer; 110 VAC, 60 Hz

[GY-03014-02](#) Portable heat sealer; 240 VAC, 50/60 Hz

[GY-06831-15](#) Plastic tie twists, 4"L (10.2 cm). Pack of 1000

## Amber Bags, PE

### Don't let light get to your samples

- Protect photo-sensitive samples during storage and transport
- Choose resealable zip-top or open-end styles



Size (W x L)		Thickness (mil)	Catalog number	Qty/ pk	Price/ pk
in.	cm				
<b>Resealable zip-top bags</b>					
2 x 3	5.1 x 7.6	3	<a href="#">GY-60103-00</a>	100	
3 x 5	7.6 x 12.7		<a href="#">GY-60103-01</a>		
4 x 6	10.2 x 15.2		<a href="#">GY-60103-02</a>		
5 x 8	12.7 x 20.3		<a href="#">GY-60103-03</a>		
8 x 8	20.3 x 20.3		<a href="#">GY-60103-04</a>		
8 x 14	20.3 x 35.6	3	<a href="#">GY-60103-05</a>	100	
9 x 12	22.9 x 30.5		<a href="#">GY-60103-06</a>		
12 x 12	30.5 x 30.5		<a href="#">GY-60103-07</a>		
3 x 9	7.6 x 22.9		<a href="#">GY-60103-08</a>		
<b>Open-end bags</b>					
5 x 7	12.7 x 17.8	2	<a href="#">GY-60103-09</a>	100	
6 x 10	15.2 x 25.4		<a href="#">GY-60103-11</a>		
8 x 14	20.3 x 35.6		<a href="#">GY-60103-13</a>		
22 x 18	55.9 x 45.7		<a href="#">GY-60103-14</a>		