

# Cole-Parmer®

Save  
money  
on these  
bundles!


## Get Discounted Pricing on Pipetting Bundles

Order item number 25307-00 with 10-mL pipettes


Order item number 25307-01 with 25-mL pipettes



**Bundle 25307-00 includes** Omega Zen pipette controller 25300-96 (blue) and serological pipette 13002-17 (10-mL capacity, 0.1-mL graduations, orange band, sterile, 200/cs).



**Bundle 25307-01 includes** Omega Zen pipette controller 25300-96 (blue) and serological pipette 13002-19 (25-mL capacity, 0.2-mL graduations, green band, sterile, 150/cs).



Turn thumbwheel and watch speedometer to fine-tune the speed.

[coleparmer.com](http://coleparmer.com)

# Omega Zen<sup>®</sup> Pipette Controller

- Easy-to-read LCD indicates aspirate/dispense speed, gravity mode, and battery charge
- Fine-tune speed control using pressure sensitive triggers and adjustable thumbwheel
- Maintain sterility with removable nosepiece and silicone adapter autoclavable at 121 °C
- Durable, UV-resistant plastic housing ideal for use in cleanrooms and fume hoods
- Rechargeable lithium battery provides over 9 hours of continuous use
- Use with plastic or glass pipettes from 0.1 to 100 mL
- Comes with universal power supply and plug, charging desk stand, wall-mount holder, and two sterile 0.45 µm PTFE filters

# Cole-Parmer<sup>®</sup> Sterile Serological Pipettes

- Designed for rapid filling with accuracy of ±2.00%
- Filler plug eliminates overfilling
- Constructed from transparent medical-grade polystyrene
- Sterilized by gamma irradiation and tested before lots are released
- Individually wrapped

**Not quite what you're looking for?** Here are some other options\*:

## Omega Zen Pipette Controller

Body color	Item number
Gray	<b>25300-98</b>

## Cole-Parmer Sterile Serological Pipettes

Capacity (mL)	Graduations (mL)	Band color	Qty/cs	Item number
1	0.01	Yellow	500	<b>13002-12</b>
1	0.1	Red	500	<b>13002-14</b>
2	0.01	White	500	<b>13002-15</b>
5	0.1	Blue	200	<b>13002-16</b>
50	0.5	Purple	100	<b>13002-20</b>

\*Must order separately. Product substitutions in bundles are not available at this time.

coleparmer.com

USA:  
+1.800.323.4340  
+1.847.549.7600

Canada: +1.800.363.5900  
China: +86.21.5109.9909  
France: +33 (0) 1486 37800  
Germany: +49 (0) 9377 92030

India: +1.800.266.1244  
Italy: +39 (0) 1313 89513  
UK: +44 (0) 1480.272279  
All other countries: +1.847.549.7600

4954

**Cole-Parmer<sup>®</sup>**