



DuPont™ Liveo™ Pharma-65 Platinum-Cured Silicone Tubing

DuPont Liveo Pharma-65 platinum-cured silicone tubing is designed to transfer ultra-pure liquids, air, or steam in pharmaceutical and biotechnology environments. Enhanced resistance to kinking and pressure helps maintain consistent flow, while excellent resilience and temperature stability support reliable long-term performance. The non-wetting surface preserves fluid characteristics without imparting taste or odor. Easily sterilize tubing by autoclave steam for 30 minutes at 120 °C, ethylene oxide, or gamma radiation at 50 kGy.



CERTIFICATION

USP Class VI, FDA 21 CFR, and ISO 10993
(Sections 3, 4, 5, 6, 10, and 11) compliant

APPLICATIONS

- Ultra-pure fluid transfer, steam or gas transfer, and filling machines

FEATURES/BENEFITS

- Excellent flexibility with enhanced pressure and kink resistance
- Non-wetting (hydrophobic) surface reduces fluid hold-up and product loss
- Flexible tubing with a 65 Shore A durometer
- Sterilize by autoclave, ethylene oxide (EtO) gas, or gamma radiation
- Free from organic plasticizers, phthalates, or latex additives
- Translucent tubing—perfect for visual monitoring

WARNING

This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
India	+1.800.266.1244
China	+86.21.5109.9909

UK	+44 (0) 1480.272279
	+33 (0) 1 87 17 01 42*
	+49 (0) 937 792030*
Italy	+39.02.84349215
All others	+1.847.549.7600

Specification and Ordering Table

Brand	Dimensions: in. (mm)			Reel length (ft)	Item number
	Tubing ID	Tubing OD	Wall		
DuPont Liveo	1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	50	50121-98
	3/16" (4.8)	5/16" (8)	1/16" (1.6)	50	50122-00
	3/16" (4.8)	3/8" (9.5)	3/32" (2.4)	50	50121-99
	1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	50	50122-02
	1/4" (6.4)	7/16" (11.1)	3/32" (2.4)	50	50122-03
	1/4" (6.4)	1/2" (12.7)	1/8" (3.2)	50	50122-01
	3/8" (9.5)	5/8" (15.9)	1/8" (3.2)	50	50122-04
	1/2" (12.7)	3/4" (19.1)	1/8" (3.2)	50	50122-05
	3/4" (19.1)	1" (25.4)	1/8" (3.2)	50	50122-06

PHARMA-65 TUBING

