

DuPont™ Liveo™ Pharma-80 Platinum-Cured Silicone Tubing

Built for demanding fluid transfer processes, DuPont™ Liveo™ Pharma-80 platinum-cured silicone tubing delivers enhanced durability and pressure resistance for pharmaceutical and bioprocessing applications. Its higher durometer construction and excellent flexibility support reliable performance and long service life in processes with rigorous operating conditions. Easily sterilize tubing by autoclave steam for 30 minutes at 120 °C, ethylene oxide, or gamma radiation at 50 kGy.



CERTIFICATION

USP Class VI, FDA 21 CFR, and ISO 10993
(Sections 3, 4, 5, 6, 10, and 11) compliant

APPLICATIONS

- Steam and gas transfer, cleanroom processing, and filtration

FEATURES/BENEFITS

- Designed for mechanical strength, pressure resistance, and durability
- Non-wetting (hydrophobic) surface reduces fluid hold-up and product loss
- Flexible tubing with an 80 Shore A durometer
- Sterilize by autoclave, ethylene oxide (EtO) gas, or gamma radiation
- Free from organic plasticizers, phthalates, or latex additives
- Translucent tubing—perfect for visual monitoring

WARNING

This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

USA

+1.800.323.4340

+1.847.549.7600

Canada

+1.800.363.5900

India

+1.800.266.1244

China

+86.21.5109.9909

UK

+44 (0) 1480.272279

+33 (0) 1 87 17 01 42*

+49 (0) 937 792030*

Italy

+39.02.84349215

All others

+1.847.549.7600

Specification and Ordering Table

Brand	Dimensions: in. (mm)			Reel length (ft)	Item number
	Tubing ID	Tubing OD	Wall		
DuPont Liveo	1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	50	50122-07
	3/16" (4.8)	5/16" (8)	1/16" (1.6)	50	50122-08
	1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	50	50122-10
	1/4" (6.4)	1/2" (12.7)	1/8" (3.2)	50	50122-09
	3/8" (9.5)	1/2" (12.7)	1/16" (1.6)	50	50122-11
	3/8" (9.5)	9/16" (14.3)	3/32" (2.4)	50	50122-13
	3/8" (9.5)	5/8" (15.9)	1/8" (3.2)	50	50122-12
	1/2" (12.7)	3/4" (19.1)	1/8" (3.2)	50	50122-14
	5/8" (15.9)	7/8" (22.2)	1/8" (3.2)	50	50122-16
	3/4" (19.1)	1" (25.4)	1/8" (3.2)	50	50122-15

PHARMA-80 TUBING

