

DuPont™ Liveo™ Pharma TPE Tubing

DuPont™ Liveo™ Pharma TPE tubing is designed for single-use pharmaceutical and biotechnology applications requiring flexible, aseptic fluid transfer. Its heat-weldable construction simplifies the creation of single-use assemblies and enables aseptic connection and disconnection without connectors. High tensile strength pre and post welding supports dependable media and solvent transport, while minimal particle generation during pumping preserves fluid purity. Easily sterilize tubing by autoclave steam for 30 minutes at 121 °C, ethylene oxide, or gamma radiation at 50 kGy. Tubing properties maintain stable when exposed to autoclave or gamma sterilization.



CERTIFICATION

Meets USP Class VI, FDA 21 CFR, and ISO 10993 (Sections 5, 6, 11, and 23) compliant

APPLICATIONS

- Peristaltic pumping, single-use assemblies, and solvent transport

FEATURES/BENEFITS

- Heat-weldable for single-use system integration
- Minimum spallation after 24 hours of pumping
- Flexible tubing with a 65 Shore A durometer
- Sterilize by autoclave, ethylene oxide (EtO) gas, or gamma radiation
- Free from phthalates or latex additives
- Good consistent clarity—perfect for visual monitoring

WARNING

This product is not approved or intended for, and should not be used for, medical, clinical, surgical, or other patient-oriented applications.

USA

+1.800.323.4340

+1.847.549.7600

Canada

+1.800.363.5900

India

+1.800.266.1244

China

+86.21.5109.9909

UK

+44 (0) 1480.272279

+33 (0) 1 87 17 01 42*

+49 (0) 937 792030*

Italy

+39.02.84349215

All others

+1.847.549.7600

Specification and Ordering Table

Brand	Dimensions: in. (mm)			Item number	Reel length (ft)
	Tubing ID	Tubing OD	Wall		
DuPont Liveo	1/8" (3.2)	1/4" (6.4)	1/16" (1.6)	50122-30	50
	3/16" (4.8)	5/16" (8)	1/16" (1.6)	50122-31	50
	1/4" (6.4)	3/8" (9.5)	1/16" (1.6)	50122-33	50
	1/4" (6.4)	7/16" (11.1)	3/32" (2.4)	50122-34	50
	1/4" (6.4)	1/2" (12.7)	1/8" (3.2)	50122-32	50
	3/8" (9.5)	9/16" (14.3)	3/32" (2.4)	50122-36	50
	3/8" (9.5)	5/8" (15.9)	1/8" (3.2)	50122-35	50
	1/2" (12.7)	11/16" (17.5)	3/32" (2.4)	50122-37	50
	1/2" (12.7)	3/4" (19.1)	1/8" (3.2)	50122-38	50
	3/4" (19.1)	1" (25.4)	1/8" (3.2)	50122-39	50

PHARMA TPE TUBING

