



Adapters, Bulkheads & Panel Mounts

**THREADED ADAPTERS | BRITISH THREADED ADAPTERS |
SCHEDULE 80 ADAPTERS | PANEL MOUNT & BULKHEAD ADAPTERS & NUTS
GARDEN HOSE ADAPTERS | NIPPLES | PLUGS | COLOR CODE CLIPS**

Eldon James' line of threaded adapters, panel mounts, bulkhead adapters, and other fittings allows for the easy and safe connection between tubes and smooth transfer of gases, liquids, and more.

Whether you're looking to lock in your automotive oil lines, plug your medical tubing, or even get a safe, PVC-free adapter for your home's garden hose, Eldon James has the right materials for you.

Threaded barb adapter fittings create a safe connection, and the non-PVC, BPA-free plastic materials of which they are composed mean your liquids, consumers, and the environment will be safe from harmful chemicals.

The threads on our Eldon James adapters and fittings employs a difficult-to-break connection, so you can ensure you have all of the strength and more that you've come to expect from other plastic fittings.

We even have conversion nipples, insert plugs, and more medical grade fittings for times when you need to stop or route the flow of liquid or gases through your tubing.

ABOUT OUR NATURAL MATERIALS:

All Cleanroom Manufactured materials are ISO Class 7.
All QC items in this section are available as a Special Order.

Medical Nylon (MN)

Nylon, which exhibits excellent tensile strength with moderate stiffness and high impact resistance. Great for medical uses to connect multiple tubes with fuels, lubricants, and many other chemicals.

Natural Nylon (NN)

Natural Nylon exhibits excellent tensile strength with moderate stiffness and high impact resistance. Great for automotive and industrial use with fuels, lubricants, and many chemicals.

Natural Kynar® 740 (NK7)

Offers excellent chemical resistance, inherent flame resistance, high gamma radiation resistance, good UV and weather resistance, good mechanical properties, low moisture absorption and good machinability.

Polypropylene (PP)

Polypropylene is a very versatile material and formulated for biomedical and bioprocess applications. It is radiation stable and is resistant to solvents, chemicals, water and other inorganic environments.



**THREADED ADAPTERS , BULKHEAD FITTINGS , PANEL MOUNTS, PIPE NIPPLES,
GARDEN HOSE AND COLOR CODE CLIPS – THREADED COMPONENT SOLUTIONS
FOR THE MEDICAL, FOOD & BEVERAGE, AND AUTOMOTIVE INDUSTRIES.**




Conversion Nipples

HOW TO BUILD YOUR SKU (Material Codes Key on page 188)

PRODUCT NO. [MATERIAL CODE]



RN4-2GFBN



RN4-2 Conversion Nipple • 1/4 x 1/8 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN6-2 Conversion Nipple • 3/8 x 1/8 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN6-4 Conversion Nipple • 3/8 x 1/4 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN8-2 Conversion Nipple • 1/2 x 1/8 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN8-4 Conversion Nipple • 1/2 x 1/4 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN8-6 Conversion Nipple • 1/2 x 3/8 inch NPT

BN • GFBN • NK7 • NN • PVDF • WN • WP

RN16-12 Conversion Nipple • 1 x 3/4 inch NPT


BN • GFBN • NK7 • NN • PVDF • WN • WP

SALES / ORDER INQUIRIES:

970-667-2728 970-667-3204

sales@eldonjames.com

eldonjames.com/adapter-bulkhead-panel-mounts



Shop All
Adapters