


# Watson-Marlow<sup>®</sup> PVC 3-Stop Pump Tubing

Watson-Marlow PVC 3-stop pump tubing offers a cost-effective and versatile solution for a wide range of fluid handling applications. Its flexibility facilitates easy installation in different setups, while the smooth inner surface minimizes particle entrapment and buildup, ensuring consistent flow and easy cleaning. Durable and reliable, the PVC pump tubing requires minimal maintenance, reducing downtime, making it an ideal choice for efficient and cost-effective fluid handling.

Stops on the tubing are color-coded according to the tubing's inside diameter for easy size identification and ensure a perfect fit on your pump head. Three stops on the tubing offer two pump segments, doubling the life of the tubing.

## PVC 3-STOP PUMP TUBING



## APPLICATIONS

- Perfect for chemical handling and use in peristaltic pumps
- Ideal for general-purpose, laboratory, and single-use applications

## FEATURES/BENEFITS

- Designed for use in Watson-Marlow multichannel pump heads
- Smooth inner surface reduces the risk of particle entrapment, ensuring consistent flow and easy cleaning
- Operating temperature range of 0 to 60 °C (32 to 140 °F)
- Flexible tubing with a 50 Shore A durometer
- Translucent tubing provides good clarity for flow monitoring
- Free technical application support available to assist with tubing selection

USA	+1.800.323.4340
	+1.847.549.7600
Canada	+1.800.363.5900
China	86.21.5109.9909
French speaker	+33 (0) 1 87 17 01 42

German speaker	+49 (0) 937 792030
India	+1.800.266.1244
Italy	+39.02.84349215
UK	+44 (0) 1480.272279
All others	+1.847.549.7600

## Specification and Ordering Table

Brand	Tubing ID: mm	Color-coded stops	Item number	Tubes per pack
Watson-Marlow	0.13	Orange/Black	<a href="#">50130-52</a>	12
	0.19	Orange/Red	<a href="#">50130-53</a>	12
	0.25	Orange/Blue	<a href="#">50130-54</a>	12
	0.38	Orange/Green	<a href="#">50130-55</a>	12
	0.50	Orange/Yellow	<a href="#">50130-56</a>	12
	0.63	Orange/White	<a href="#">50130-57</a>	12
	0.76	Black/Black	<a href="#">50130-58</a>	12
	0.88	Orange/Orange	<a href="#">50130-59</a>	12
	1.02	White/White	<a href="#">50130-60</a>	12
	1.14	Red/Red	<a href="#">50130-61</a>	12
	1.29	Gray/Gray	<a href="#">50130-62</a>	12
	1.42	Yellow/Yellow	<a href="#">50130-63</a>	12
	1.52	Yellow/Blue	<a href="#">50130-64</a>	12
	1.65	Blue/Blue	<a href="#">50130-65</a>	12
	1.85	Green/Green	<a href="#">50130-66</a>	12
	2.05	Purple/Purple	<a href="#">50130-67</a>	12
	2.29	Purple/Black	<a href="#">50130-68</a>	12
	2.54	Purple/Orange	<a href="#">50130-69</a>	12
2.79	Purple/White	<a href="#">50130-70</a>	12	



The information contained in this document is believed to be correct but Cole-Parmer accepts no liability for any errors it contains, and reserves the right to alter specifications without notice. Watson-Marlow is a registered trademark of Watson-Marlow Limited. Please state the item number when ordering.

**Cole-Parmer**<sup>®</sup>  
an antylia scientific company