

**FDA-Compliant High-Purity Solid Stoppers, Silicone****Stop particle buildup**


Food-grade quality stoppers are nontoxic, chemically inert, and resist particle buildup. Withstand repeated sterilization, as well as temperatures from -76 to 392°F (-60 to 200°C). Peak at 428°F (220°C). European size (DIN no.) is noted on stopper. FDA compliant. Autoclavable.



**Buy More...Save More!**

20% off on 120+ 15% off on 30 to 119 10% off on 6 to 29 packs or cases

Standard size no.	European size no.	Top dia (mm)	Bottom dia (mm)	Height (mm)	Catalog number	Qty/pk	Price/pk
—	6D	6.5	3.5	15	<a href="#">GH-62994-00</a>	10	
—	8D	8	4	20	<a href="#">GH-62994-02</a>	10	
—	10D	9	5	20	<a href="#">GH-62994-04</a>	10	
000	13D	12	8	20	<a href="#">GH-62994-06</a>	10	
00	15D	14.5	10.5	20	<a href="#">GH-62994-08</a>	10	
0	16D	16.5	12.5	20	<a href="#">GH-62994-10</a>	10	
1	18D	18	14	20	<a href="#">GH-62994-12</a>	10	
2	21D	22	17	25	<a href="#">GH-62994-14</a>	10	
3	24D	24	18	30	<a href="#">GH-62994-16</a>	10	
4	27D	27	21	30	<a href="#">GH-62994-18</a>	10	
5	29D	29	23	30	<a href="#">GH-62994-20</a>	10	
6	31D	32	26	30	<a href="#">GH-62994-22</a>	10	
6½	34D	35	29	30	<a href="#">GH-62994-24</a>	5	
7	38D	38	31	35	<a href="#">GH-62994-26</a>	5	
8	41D	41	34	35	<a href="#">GH-62994-28</a>	5	
9	45D	44	36	40	<a href="#">GH-62994-30</a>	5	
10	49D	49	41	40	<a href="#">GH-62994-32</a>	2	
10½	54D	55	47	40	<a href="#">GH-62994-34</a>	2	
11	60D	59.5	50.5	45	<a href="#">GH-62994-36</a>	2	
11½	65D	65	56	45	<a href="#">GH-62994-38</a>	1	
13	70D	70	60	50	<a href="#">GH-62994-40</a>	1	
—	75D	75.5	64.5	55	<a href="#">GH-62994-42</a>	1	
—	83D	83	71	60	<a href="#">GH-62994-44</a>	1	
14	92D	92	79	65	<a href="#">GH-62994-46</a>	1	
15	100D	100	87	65	<a href="#">GH-62994-48</a>	1	
—	107D	107	94	65	<a href="#">GH-62994-50</a>	1	

**Stopper Hole Borer Sets and Sharpener****Easily convert solid stoppers to holed stoppers**

Description	Number of borers	Boring dia range (mm)	Material	Catalog number	Price
Small cork borer set	6	4 to 10	Chrome-plated brass	<a href="#">GH-06298-97</a>	
Medium cork borer set	9	4 to 15	Chrome-plated brass	<a href="#">GH-06298-98</a>	
Large cork borer set	12	4 to 22	Chrome-plated brass	<a href="#">GH-06298-99</a>	
Medium borer set	9	4.5 to 13	Brass	<a href="#">GH-06298-91</a>	
Large borer set	12	5 to 21.5	Steel	<a href="#">GH-06298-90</a>	
Borer sharpener	—	—	Brass	<a href="#">GH-06298-94</a>	

**Folding Skirt Stoppers, Rubber or Silicone****Stay watertight even after several perforations**

– Easily extract contents by perforating stopper

The lower section is molded to grip the outside of the container and the upper hollow plug features annular serrations to provide a tight seal at the rim. **Rubber Stoppers** are ideal for chemical transfer and withstand temperatures from -4 to 212°F (-20 to 100°C). **Silicone Stoppers** are chemical resistant and withstand temperatures from -76 to 428°F (-60 to 220°C).



Natural rubber stoppers

**Buy More...Save More!**

20% off on 120+  
15% off on 30 to 119  
10% off on 6 to 29 packs or cases

Max OD (mm)	Top dia (mm)	Bottom dia (mm)	Height (mm) <sup>†</sup>	Catalog number	Qty/pk	Price/pk
<b>Natural rubber stoppers</b>						
7.1	7.5	4.5	9/8	<a href="#">GH-62995-80</a>	100	
10.2	10.7	9.8	14/9	<a href="#">GH-62995-81</a>	50	
12.7	13.3	12.3	20/10	<a href="#">GH-62995-82</a>	50	
14.9	15.5	14.2	20/11	<a href="#">GH-62995-83</a>	20	
<b>Clear silicone stoppers</b>						
7.1	7.4	4.5	9/8	<a href="#">GH-62995-90</a>	100	
10.2	10.7	9.8	14/9	<a href="#">GH-62995-91</a>	50	
12.7	13.3	12.3	20/10	<a href="#">GH-62995-92</a>	50	
14.9	15.5	14.2	20/11	<a href="#">GH-62995-93</a>	20	

<sup>†</sup>The first measurement is from the outer edge to the middle. The second measurement is from the middle to the top.

**Scienceware® Stoppers and Adapters, PTFE/PP/Viton®****No more stuck stoppers, no more broken glassware!**

- Easy, safe removal of stoppers and adapters from your flasks
- Unbreakable—consist of a body of chemically inert PTFE, threaded polypropylene extracting nut, and Viton O-ring

**§ Joint Stirrer Bearing**

Use with 10-mm OD stirring rods. Use O-ring for fine adjustment of rod tension. Threaded PP locking compression cap. Removable bushing fits inside adapter (extra bushing included).

Taper size	Catalog number	Price/ea
24/40	<a href="#">GH-06139-85</a>	

§ Symbol used to designate interchangeable joints, stoppers, and stopcocks that comply with the requirements of Commercial Standard CS-21 published by NIST.

**§ Joint Thermometer and Tubing Adapters**

For air-tight vacuum work. Threaded PP screw cap on top with an inside O-ring for fine depth adjustment of thermometers or tubing.

Taper size	Port ID	Catalog number	Price/ea
<b>Thermometer adapters</b>			
14/20	6 to 7 mm	<a href="#">GH-06140-10</a>	
19/22		<a href="#">GH-06140-20</a>	
24/40		<a href="#">GH-06140-22</a>	
<b>Tubing adapters</b>			
24/40	8 mm	<a href="#">GH-06140-52</a>	
	10 mm	<a href="#">GH-06140-53</a>	