

Dow Corning® Pharma-80 Tubing

Economical alternative to reinforced tubing



Applications: High-pressure, pharmaceutical, biotech, and ultra-pure fluid processing.

Characteristics: 80 durometer, semi-transparent platinum-cured silicone tubing with a very low extractable profile; it contains no phthalates, plasticizers, latex or other organic additives. Pharma tubing is hydrophobic, and remains flexible and resilient for long service life. Dow Corning maintains complete traceability from silica to silicone tubing.

Certifications: Elastomer exceeds test guidelines for USP Class VI Plastics; tubing itself meets or exceeds FDA (21 CFR 177.2600), 3A Sanitary Standards, and European Pharmacopoeia (EP) requirements. Pharma tubing is produced under Bulk Pharmaceutical (BP) current GMP principals.

Temperature range: -60 to 460°F (-51 to 232°C)

Sterilize: Autoclave, ethylene oxide, or gamma irradiation.

Buy More...Save More!
20% off on 20+ 15% off on 10 to 19 10% off on 4 to 9 packs

Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/ 50-ft pk
ID	OD	Wall			
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	249 (17.2)	GH-96109-00	
3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	249 (17.2)	GH-96109-01	
3/16 (4.8)	3/8 (9.6)	3/32 (2.4)	260 (17.9)	GH-96109-02	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	249 (17.2)	GH-96109-03	
1/4 (6.4)	7/16 (11.2)	3/32 (2.4)	249 (17.2)	GH-96109-04	
1/4 (6.4)	1/2 (12.8)	1/8 (3.2)	260 (17.9)	GH-96109-05	
5/16 (8.0)	1/2 (12.8)	3/32 (2.4)	249 (17.2)	GH-96109-06	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	241 (16.6)	GH-96109-07	
3/8 (9.6)	9/16 (14.4)	3/32 (2.4)	249 (17.2)	GH-96109-08	
3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	231 (15.9)	GH-96109-09	
1/2 (12.8)	11/16 (17.6)	3/32 (2.4)	210 (14.5)	GH-96109-10	
1/2 (12.8)	3/4 (19.1)	1/8 (3.2)	200 (13.8)	GH-96109-11	

Platinum-Cured Silicone Tubing Spools

Cut tubing to your needs



Dimensions in. (mm)		Length per spool	Catalog number	Price
ID	OD			
1/32 (0.8)	3/32 (2.4)	500 ft (152 m)	GH-98906-00	
1/16 (1.6)	1/8 (3.2)		GH-98906-02	
1/8 (3.2)	1/4 (6.4)	300 ft (91 m)	GH-98906-04	
3/16 (4.8)	5/16 (8.0)		GH-98906-06	
1/4 (6.4)	3/8 (9.6)		GH-98906-08	
3/8 (9.6)	5/8 (16.0)		GH-98906-10	
5/8 (16.0)	7/8 (22.4)		GH-98906-12	

Ratchet Tubing Clamps

Durable Celcon® plastic tubing clamps are autoclavable; won't rust, corrode, or distort. Twelve-position ratchet control adjusts from full flow to complete closure. Mini-clamp is suitable for up to 1/8" (2.1 mm) OD tubing. Standard clamp accepts flexible tubing to 1/2" (12.7 mm) OD.



06833-00

[GH-06833-01](#) Mini tubing clamp. Pack of 25
[GH-06833-00](#) Tubing clamp. Pack of 25

Dow Corning® Pharma-65 Tubing

Resilient for extended service life



Applications: High-pressure, pharmaceutical, biotechnology, and ultra-pure fluid processing.

Characteristics: 65 durometer, platinum-cured silicone tubing with a very low extractable profile; it contains no phthalates, plasticizers, latex, or other organic additives. Remains flexible and resilient for long service life. Dow Corning maintains complete traceability from silica to silicone tubing.

Certifications: Elastomer is FDA-compliant (21 CFR 177.2600) and meets USP Class VI requirements. Meets 3A Sanitary Standards and European Pharmacopoeia (EP) requirements. Tubing is manufactured according to Bulk Pharmaceutical (BP) and current GMP.

Temperature range: -60 to 460°F (-51 to 232°C)

Sterilize: Autoclave, ethylene oxide, or gamma irradiation.

Buy More...Save More!
20% off on 20+ 15% off on 10 to 19 10% off on 4 to 9 packs

Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/ 50-ft pk
ID	OD	Wall			
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	19 (1.3)	GH-96107-00	
3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	13 (0.9)	GH-96107-01	
3/16 (4.8)	3/8 (9.6)	3/32 (2.4)	15 (1.0)	GH-96107-02	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	10 (0.7)	GH-96107-03	
1/4 (6.4)	7/16 (11.2)	3/32 (2.4)	20 (1.4)	GH-96107-04	
1/4 (6.4)	1/2 (12.8)	1/8 (3.2)	19 (1.3)	GH-96107-05	
5/16 (8.0)	1/2 (12.8)	3/32 (2.4)	12 (0.8)	GH-96107-06	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	11 (0.8)	GH-96107-07	
3/8 (9.6)	9/16 (14.4)	3/32 (2.4)	13 (0.9)	GH-96107-08	
3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	13 (0.9)	GH-96107-09	
1/2 (12.8)	11/16 (17.6)	3/32 (2.4)	12 (0.8)	GH-96107-10	
1/2 (12.8)	3/4 (19.1)	1/8 (3.2)	11 (0.8)	GH-96107-11	
3/4 (19.1)	7/8 (22.4)	1/8 (3.2)	8 (0.6)	GH-96107-12	
3/4 (19.1)	1 (25.4)	1/8 (3.2)	7 (0.5)	GH-96107-13	

Dow Corning® Pharma-50 Tubing

No organic additives and low extractables



Applications: Pharmaceutical, biotechnology, and ultrapure fluid processing.

Characteristics: 50 durometer, translucent platinum-cured silicone tubing with a very low extractable profile. Pharma tubing remains flexible and resilient for long service life. Dow Corning maintains complete traceability from silica to silicone tubing.

Certifications: Elastomer exceeds test guidelines for USP Class VI Plastics and the tubing itself meets or exceeds FDA (21 CFR 177.2600), 3A Sanitary Standards and European Pharmacopoeia (EP) requirements. Produced under Bulk Pharmaceutical (BP) and current GMP principals.

Temperature range: -60 to 460°F (-51 to 232°C)

Sterilize: Autoclave, ethylene oxide, or gamma irradiation.

Buy More...Save More!
20% off on 20+ 15% off on 10 to 19 10% off on 4 to 9 packs

Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/ 50-ft pk
ID	OD	Wall			
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	21 (1.4)	GH-96105-00	
3/16 (4.8)	3/8 (9.6)	3/32 (2.4)	16 (1.1)	GH-96105-02	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	12 (0.8)	GH-96105-03	
1/4 (6.4)	7/16 (11.1)	3/32 (2.4)	17 (1.2)	GH-96105-04	
1/4 (6.4)	1/2 (12.8)	1/8 (3.2)	17 (1.2)	GH-96105-05	
5/16 (8.0)	1/2 (14.0)	1/8 (3.0)	16 (1.1)	GH-96105-06	
3/8 (9.6)	9/16 (14.3)	3/32 (2.4)	13 (0.9)	GH-96105-08	
3/8 (9.6)	5/8 (16.0)	1/8 (3.2)	14 (1.0)	GH-96105-09	
1/2 (12.8)	3/4 (19.1)	1/8 (3.2)	10 (0.7)	GH-96105-11	
5/8 (16.0)	7/8 (22.2)	1/8 (3.2)	9 (0.6)	GH-96105-12	