

Sterile Single-Use Tank Liners, LLDPE

No more washing, cleaning, or revalidation

- Ready for immediate use
- Save money and time—no need for expensive equipment
- Manufactured with LLDPE, liners are pyrogen-free



Gallons (liters)	Dimensions	Catalog number	Qty/pk	Price/pk
13.2 (50)	27"H x 13" OD	GH-06310-01	40	
34.4 (130)	30"H x 18" OD	GH-06310-02	20	
52.8 (200)	36"H x 22" OD	GH-06310-04	20	
79.3 (300)	48"H x 24" OD	GH-06310-06	20	
106 (401)	44"H x 28" OD	GH-06310-08	20	
148 (560)	49"H x 31" OD	GH-06310-10	10	
198 (750)	51"H x 36" OD	GH-06310-12	10	
264 (1000)	49"H x 42" OD	GH-06310-14	10	
343 (1298)	49"H x 48" OD	GH-06310-16	10	

Seamless Drums, LLDPE

No more heavy steel drums

- Withstand rough handling—lightweight, rugged design
- Easy access through 2" and 3/4" NPT bungs
- Tough sides can support mixer

Tight-head drum models 06950-40 and -50 are 1H1 single packages complying with UN specifications; all meet HM-181 and IATA Specification Packaging Standards.

Open-head drums feature a removable lid sealed by a neoprene gasket; a polycoated steel ring with threaded tightening bolt securely fastens lid to drum (lid, gasket, and steel ring included).

Gallons (liters)	Dimensions		Wall thickness	Catalog number	Price
	Height	Rib diameter			
Tight-head drums					
15 (57)	22½" (57.2 cm)	15¾" (40 cm)	0.120"	GH-06950-10	
30 (114)	29¾" (75.6 cm)	19" (48.3 cm)	0.188"	GH-06950-20	
55 (208)	36¾" (93.3 cm)	23" (58.4 cm)	0.250"	GH-06950-30	
HM-181 specification (1H1) tight-head drums					
30 (114)	29¾" (75.6 cm)	19¾" (50.2 cm)	0.190"	GH-06950-40	
55 (208)	36¾" (92.1 cm)	23¾" (60.3 cm)	0.190"	GH-06950-50	
Resealable open-head drums					
15 (57)	23¾" (60.3 cm)	15¾" (40 cm)	0.120"	GH-06950-15	
30 (114)	31⅞" (81.1 cm)	19" (48.3 cm)	0.187"	GH-06950-25	
55 (208)	37½" (95.3 cm)	23" (58.4 cm)	0.250"	GH-06950-35	

Adjustable Wrap-Around Tote Tank/IBC Blanket Heaters

Don't let your product get cold

Provide fast uniform heat to your tote tank/IBC contents with these wrap-around blanket heaters. The full-coverage plug and play system is constructed of a silicone-impregnated cloth facing and liner with a ¼"-thick fiberglass insulation, and is intended for indoor use.

Blanket height	Temperature range	Power			Catalog number	Price
		VAC	Watts	Amps		
36" (91 cm)	50 to 160°F (10 to 71°C)	120	1440	12	GH-09302-05	
42" (107 cm)					GH-09302-10	
48" (122 cm)					GH-09302-15	



Cylindrical Closed-Dome Tanks, HDPE and PP

Be compliant with FDA Regulation 177.1520

- Know how much remains—graduations for easy volume readings

All tanks have a threaded screw closure with gasket that securely fits the 6¼" fill well. Two mounting flats near the bottom, set 180° apart, permit installation of a bulkhead fitting up to 2". Domed bottom drains fluid into narrow trough around base rim.



High-Density Polyethylene (HDPE)

Tanks have a 2" bung with cap on the top that permits access for tubing or piping.

Polypropylene Tanks can be repeatedly autoclaved.

Gallons (liters)	Dimensions (H x OD)	Graduations gal. (liters)	Catalog number	Wall	Price
HDPE closed-dome tanks					
30 (114)	36¾" x 18"	2.5 (10)	GH-06318-70	0.187"	
55 (208)	39½" x 22"	2.5 (10)	GH-06318-75	0.250"	
100 (379)	51¼" x 28½"	10 (50)	GH-06318-90†	0.250"	
PP closed-dome tanks					
30 (114)	36¾" x 18"	2.5 (10)	GH-50301-52	0.250"	
55 (208)	39½" x 22"	2.5 (10)	GH-50301-54	0.250"	
100 (379)	51¼" x 28½"	10 (50)	GH-50301-56†	0.312"	

†Ship by motor freight only.

