

Chemfluor® ETFE Tubing

Stands up to your demands



Applications: Demanding lab, chemical, electrical, mechanical, and automotive applications. ETFE tubing withstands the highest pressures of all fluoropolymer tubing.

Characteristics: Chemically inert, excellent mechanical resistance, low coefficient of friction, and slightly flexible. Translucent.

Certifications: Resin meets ASTM standard D3159.

Temperature range: -150 to 300°F (-101 to 149°C)

Sterilize: Autoclave or ethylene oxide.

Buy More...Save More!
 20% off on 20+
 15% off on 10 to 19
 10% off on 4 to 9 packs

Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/50-ft pk
ID	OD	Wall			
1/50 (0.5)	1/16 (1.6)	1/64 (0.5)	975 (67.2)	GH-06488-07	
1/64 (0.4)	1/16 (1.6)	1/32 (0.8)	975 (67.2)	GH-06488-08	
3/32 (2.4)	1/8 (3.2)	3/64 (1.2)	975 (67.2)	GH-06488-09	
1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	975 (67.2)	GH-06488-10	
3/16 (4.8)	1/4 (6.4)	3/64 (1.2)	455 (31.4)	GH-06488-11	
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	455 (31.4)	GH-06488-12	
0.232 (5.9)	3/16 (8.0)	1/20 (1.1)	290 (20.0)	GH-06488-13	
0.278 (7.1)	3/8 (9.6)	3/64 (1.2)	290 (20.0)	GH-06488-14	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	215 (14.8)	GH-06488-15	

Chemfluor® 367 Tubing

Maintain fluid integrity



Applications: For pharmaceutical, semiconductor, electrical, environmental and other processes dependent on maintaining fluid integrity and high purity.

Characteristics: Exceptionally smooth surface, very low extractables with deionized water and acids, excellent chemical resistance and mechanical properties, low counts of trace metals, superior clarity.

Certifications: FDA-compliant (21 CFR 177.1550).

Temperature range: -400 to 450°F (-240 to 232°C)

Sterilize: Ethylene oxide, autoclave, or dry heat.

Buy More...Save More!
 20% off on 20+
 15% off on 10 to 19
 10% off on 4 to 9 packs

Dimensions: in. (mm)			Max psi at 73°F (bar at 23°C)	Catalog number	Price/50-ft pk
ID	OD	Wall			
1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	379 (26.1)	GH-95638-00	
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	383 (26.4)	GH-95638-01	
3/32 (4.0)	1/4 (6.4)	3/32 (2.4)	266 (18.3)	GH-95638-02	
3/16 (4.8)	1/4 (6.4)	1/32 (0.8)	163 (11.2)	GH-95638-03	
1/4 (6.4)	5/16 (8.0)	1/32 (0.8)	129 (8.9)	GH-95638-04	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	230 (15.9)	GH-95638-05	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	164 (11.3)	GH-95638-06	

Custom Cut Tubing
For details, call 800-323-4340

Cole-Parmer® PFA Tubing

Stands up to highly corrosive materials



Applications: Demanding lab, chemical, electrical, mechanical, pharmaceutical, and automotive applications. For the transfer of high-temperature or highly corrosive materials. Also good for high-purity work.

Characteristics: Chemically inert, nontoxic, and virtually nonporous. Excellent crack- and stress-resistance. Low coefficient of friction. Translucent.

Certifications: Resin is FDA-compliant (21 CFR 177.1550). Tubing is manufactured in ISO 9001-2008 approved facility.

Temperature range: -320 to 500°F (-195 to 260°C)

Sterilize: Autoclave, ethylene oxide, or dry heat.

Buy More...Save More!
 20% off on 20+
 15% off on 10 to 19
 10% off on 4 to 9 packs



Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/25-ft pk
ID	OD	Wall			
1/32 (0.8)	1/16 (1.6)	1/64 (0.4)	600 (41.4)	GH-06371-00	
1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	592 (40.8)	GH-06375-01	
3/32 (2.4)	5/32 (4.0)	1/32 (0.8)	471 (32.5)	GH-06371-01	
1/8 (3.2)	3/16 (4.8)	1/32 (0.8)	385 (26.5)	GH-06371-02	
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	600 (41.4)	GH-06371-21	
5/32 (4.0)	1/4 (6.4)	3/64 (1.2)	421 (29.0)	GH-06375-02	
3/16 (4.8)	1/4 (6.4)	1/32 (0.8)	280 (19.3)	GH-06371-03	
3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	471 (32.5)	GH-06371-22	
1/4 (6.4)	5/16 (8.0)	1/32 (0.8)	220 (15.2)	GH-06371-04	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	388 (26.8)	GH-06375-05	
1 9/64 (7.5)	3/8 (9.6)	3/28 (1.0)	229 (15.8)	GH-06371-23	
5/16 (8.0)	3/8 (9.6)	1/32 (0.8)	180 (12.4)	GH-06371-05	
5/16 (8.0)	7/16 (11/2)	1/16 (1.6)	324 (22.3)	GH-06371-24	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	283 (19.5)	GH-06375-07	
3/8 (10.2)	1/2 (12.8)	1/20 (1.2)	220 (9.5)	GH-06371-25	
7/16 (11/2)	1/2 (12.8)	1/32 (0.8)	133 (9.2)	GH-06371-07	
1/2 (12.8)	5/8 (16.0)	1/16 (1.6)	220 (15.2)	GH-06371-26	
5/8 (16.0)	3/4 (19.0)	1/16 (1.6)	150 (10.3)	GH-06375-08	
1 1/16 (17.5)	3/4 (19.0)	1/32 (0.8)	87 (6.0)	GH-06371-28	
3/4 (19.0)	7/8 (22.2)	1/16 (1.6)	153 (10.5)	GH-06371-29	

Cole-Parmer® High-Purity PFA-450 Tubing

Won't crack under stress



Applications: Pharmaceutical, biotechnology, environmental, semiconductor processing, food and beverage, autoanalyzer, and nuclear applications.

Characteristics: Superior surface smoothness and clarity, low extractables with deionized water and acids, high resistance to stress and cracking. Translucent.

Certifications: Resin is FDA-compliant (21 CFR 177.1550). Tubing is manufactured according to GMP.

Temperature range: -195 to 260°C (-320 to 500°F)

Sterilize: Autoclave, ethylene oxide, gamma irradiation, and dry heat.

Buy More...Save More!
 20% off on 20+
 15% off on 10 to 19
 10% off on 4 to 9 packs



Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/25-ft pk
ID	OD	Wall			
1/16 (1.6)	1/8 (3.2)	1/32 (0.8)	592 (40.8)	GH-06368-50	
1/8 (3.2)	3/16 (4.8)	1/32 (0.8)	387 (26.7)	GH-06368-51	
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	600 (41.4)	GH-06368-52	
3/32 (4.0)	1/4 (6.4)	3/64 (1.2)	420 (29.0)	GH-06368-53	
3/16 (4.8)	1/4 (6.4)	1/16 (1.6)	278 (19.2)	GH-06368-54	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	389 (26.8)	GH-06368-55	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	283 (19.5)	GH-06368-56	
1/2 (12.8)	5/8 (16.0)	1/16 (1.6)	220 (15.2)	GH-06368-57	
5/8 (16.0)	3/4 (19.2)	1/16 (1.6)	149 (10.3)	GH-06368-58	
3/4 (19.2)	7/8 (22.4)	1/16 (1.6)	141 (9.7)	GH-06368-59	
7/8 (22.4)	1 (25.4)	1/16 (1.6)	133 (9.2)	GH-06368-60	