


Cole-Parmer® Coiled FEP Tubing

Retracts for easier handling



Our retractable coil FEP tubing offers the chemical inertness of our standard FEP tubing combined with the flexibility of a coil. FEP tubing has excellent heat resistance, and a low coefficient of friction. Tubing withstands temperatures from -454 to 400°F (-270 to 205°C); and can be sterilized by autoclave, with ethylene oxide, or by using dry heat. Choose the size and length that best fits your application. Use tubing with compression fittings. See our "Fittings" section on pages 264-305.



Dimensions: in. (mm)				Max psi at 77°F (bar at 25°C)	Catalog number	Price
ID	OD	Wall	Coil ID			
Coiled FEP tubing, 12" relaxed/24" expanded length						
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	1 (25.4)	450 (31.0)	GH-95821-00	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	1 3/4 (44.5)	318 (21.9)	GH-95821-02	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	3 (76.2)	210 (14.5)	GH-95821-04	
Coiled FEP tubing, 24" relaxed/48" expanded length						
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	1 (25.4)	450 (31.0)	GH-95821-01	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	1 3/4 (44.5)	318 (21.9)	GH-95821-03	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	3 (76.2)	210 (14.5)	GH-95821-05	

Cole-Parmer® Corrugated FEP Tubing

No kinks or distortion



High flexibility and excellent chemical resistance. Corrugations prevent kinking and help tubing retain its shape without limiting pressure or vacuum abilities. Simply cut this custom-extruded tubing to desired length. Sold in 5-ft lengths; each length has alternating sections of corrugated (10"L) and noncorrugated (2"L) tubing, with noncorrugated 1"L sections at both ends. Temperature range: -300 to 400°F (-184 to 205°C). Withstands 27" Hg vacuum.



Cuff ID	Cuff OD	Wall	Max psi at 70°F (bar at 21°C)	Catalog number	Price/ 5-ft length*
Tubing compatible with barbed fittings					
1/4"	9/32"	1/64"	250 (17.2)	GH-06407-50	
3/8"	13/32"	1/32"	200 (13.8)	GH-06407-52	
Tubing compatible with compression fittings					
7/32"	1/4"	1/64"	250 (17.2)	GH-06407-60	
21/64"	3/8"	1/32"	200 (13.8)	GH-06407-62	
29/64"	1/2"	1/32"	170 (11.7)	GH-06407-64	
11/16"	3/4"	1/32"	120 (8.3)	GH-06407-66	

*Discounts: Save 10% on 10 to 49, 15% on 50 to 99, and 20% on 100 5-ft lengths or more.

Cole-Parmer® Kynar® PVDF Tubing

Fluoropolymer tubing at less cost



Applications: High-purity applications and corrosive chemical transfer—an inexpensive alternative to other fluoropolymer tubing.
Characteristics: Polyvinylidene fluoride (PVDF) material is kink resistant; has excellent chemical resistance, and is odorless and nontoxic. Translucent.
Certifications: Resin is FDA-compliant (21 CFR 177.2600); meets USP Class VI and USDA requirements.
Temperature range: -40 to 260°F (-40 to 127°C)
Sterilize: Autoclave and gamma irradiation.

Buy More... Save More!
 \$ 20% off on 20+
 15% off on 10 to 19
 10% off on 4 to 9 packs



Dimensions: in. (mm)			Max psi at 70°F (bar at 21°C)	Catalog number	Price/ 25-ft pk
ID	OD	Wall			
1/8 (3.2)	1/4 (6.4)	1/16 (1.6)	350 (24.1)	GH-95100-00	
11/64 (4.2)	1/4 (6.4)	3/64 (1.2)	180 (12.4)	GH-95100-02	
3/16 (4.8)	5/16 (8.0)	1/16 (1.6)	290 (20.0)	GH-95100-04	
1/4 (6.4)	3/8 (9.6)	1/16 (1.6)	240 (16.5)	GH-95100-06	
3/8 (9.6)	1/2 (12.8)	1/16 (1.6)	180 (12.4)	GH-95100-10	
1/2 (12.8)	3/8 (16.0)	1/16 (1.6)	145 (10.0)	GH-95100-12	
5/8 (16.0)	3/4 (19.2)	1/16 (1.6)	120 (8.3)	GH-95100-14	
3/4 (19.2)	7/8 (22.2)	1/16 (1.6)	100 (6.9)	GH-95100-16	

Handheld Tubing Cutter

Steel blade coated with PTFE resin produces clean, straight cuts through tubing up to 1 1/4" OD (cuts polyethylene tubing up to 1 1/2" OD). Order carrying pouch and replacement blade separately below.



Description	Catalog number	Price
Handheld tubing cutter	GH-06438-90	
Tubing cutter pouch	GH-06438-81	
Replacement blade for handheld tubing cutter	GH-06438-92	

Wait!

There's More at
[ColeParmer.com](#)

Browse 100,000+ products plus find
Technical Resources to help you choose