

Digi-Sense™ Precalibrated Compact Vane Anemometer

Lightweight and pocket-sized for convenient field use

- Reliable measurements, guaranteed! Precalibrated to NIST-traceable standards
- Backlight sensor is automatically activated by low-light conditions
- Max/Avg functions to easily manage airflow measurement
- User-selectable units of measure eliminate the need for conversion

NEW



DIGI-SENSE™

Description	Compact vane anemometer
Catalog number	GY-20250-23
Range	80 to 5900 ft/min (1.1 to 30 m/s)
Resolution	1 ft/min (0.01 m/s)
Accuracy	±(3% + 40 ft/min) [±(3% + 0.20 m/s)]
Units, selectable	ft/min, m/s, mph, km/h, knots
Sampling rate	Approximately once per second
Power	One 9 V battery
Price	

Digi-Sense™ Precalibrated Data Logging Anemometer

Be more versatile—handheld or mountable

- Reliable measurements, guaranteed! Precalibrated to NIST-traceable standards
- Analyze and graph logged data using included software
- Two start modes: automatic and manual
- User-defined high and low alarm levels with visual LED indication
- Articulated screw-on mounting stand provides flexible positioning

NEW



DIGI-SENSE™

Description	Data logging anemometer
Catalog number	GY-20250-22
Range	80 to 3837 ft/min (1.1 to 20 m/s)
Resolution	1 ft/min (0.01 m/s)
Accuracy	±(3% + 40 ft/min) [±(3% + 0.20 m/s)]
Units, selectable	ft/min, m/s, mph, km/h, knots
Memory	32,000 readings
Sampling rate	Once every 2 seconds to once every 24 hours
Power	One 3.6 V lithium battery
Price	

Digi-Sense™ Precalibrated CFM/CMM Vane Thermoanemometer

Get high precision with large backlit LCD and data storage

- Reliable measurements, guaranteed! Precalibrated to NIST-traceable standards
- User-selectable units of measure eliminate the need for conversion
- Two memory locations, one CMM and one CFM, store commonly used vent area sizes to save you time
- Large dual-function 4-digit LCD with backlight for easy reading
- Auto power-off extends battery life
- Fits comfortably in your hand

NEW



DIGI-SENSE™

The Digi-Sense CFM/CMM vane thermoanemometer is designed for precision air velocity and airflow measurements in seven user-selectable units of measurement (ft/min, m/s, mph, km/h, knots, CFM, and CMM). The instrument will help you meet cooling and environmental requirements for safety and comfort. The large dual display allows you to simultaneously read air velocity or airflow, and air temperature (°F/°C).

Description	CFM/CMM vane thermoanemometer	
Catalog number	GY-20250-14	
Air velocity	Range	80 to 5900 ft/min (0.4 to 30 m/s)
	Resolution	1 ft/min (0.01 m/s)
	Accuracy	±(3% + 40 ft/min) [±(3% + 0.20 m/s)]
Airflow	Range	0 to 999,900 CFM (0 to 999,900 CMM)
	Resolution	0.001 to 100 CFM/CMM
Temperature	Range	32 to 122°F (0 to 50°C)
	Resolution	0.1°F/°C
	Accuracy	4.0°F (2.0°C)
Units, selectable	ft/min, m/s, mph, km/h, knots, CFM, CMM, °F, °C	
Airflow memory	Two commonly used area sizes (one for CFM, one for CMM)	
Sampling rate	Approximately once per second	
Power	Three AAA batteries, 40 hours typical	
Price		

Save time, save money!

Choose Precalibrated
Includes a data-rich, ISO 17025 certificate—no additional charge!

Precalibrated by **INNOCAL®**
INNOVATIVE CALIBRATION SOLUTIONS