

**032-15-GL**

**FLOWMETER CALIBRATION DATA**

**032/53**

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		0787-A1-AM-04N

Max. Flow	Min. Flow	Units	Metering Fluid	Date
59.2	1.20	std. ml/min	carbon dioxide	30-Nov-1999

<b>Model Number</b>		<b>Metering Temperature</b>	70.0 °F
<b>Tube Number</b>	032-15-GL	<b>Metering Pressure</b>	14.70 psia
<b>Serial Number</b>		<b>Metering density</b>	0.001835 g/ml
<b>Float Material</b>	glass	<b>Metering Viscosity</b>	0.01470 cp
<b>Float Density</b>	2.53 g/ml	<b>Density at STD.Cond</b>	0.001835 g/ml
<b>STD. Conditions</b>	STP: 1 atm @ 70 °	<b>Accuracy</b>	std.
<b>Room Temperature</b>	70.0 °F	<b>Barometric Pressure</b>	14.70 psia

SCALE READINGS AT CENTER OF FLOAT	
Scale Reading (mm)	Flow
65	59.2
60	51.5
55	44.1
50	37.7
45	30.8
40	25.0
35	19.9
30	15.8
25	12.4
20	9.00
15	5.80
10	3.20
5	1.20