



Telephone: 847.549.7600
 800.323.4340
 Fax: 847.247.2929
 E-mail: techinfo@coleparmer.com
 Web: www.coleparmer.com

032-15-GL

FLOWMETER CALIBRATION DATA

032/62

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		0787-AI-AM-04N

Max. Flow	Min. Flow	Units	Metering Fluid	Date
99.6	6.91	std. ml/min	hydrogen	30-Nov-1999

Model Number		Metering Temperature	70.0 °F
Tube Number	032-15-GL	Metering Pressure	14.70 psia
Serial Number		Metering density	0.0000834 g/ml
Float Material	glass	Metering Viscosity	0.00885 cp
Float Density	2.53 g/ml	Density at STD.Cond	0.0000834 g/ml
STD. Conditions	STP: 1 atm @ 70 °	Accuracy	std.
Room Temperature	70.0 °F	Barometric Pressure	14.70 psia

SCALE READINGS AT CENTER OF FLOAT	
Scale Reading (mm)	Flow
65	99.6
60	88.2
55	76.8
50	64.5
45	54.0
40	45.8
35	39.4
30	32.7
25	25.4
20	18.8
15	13.0
10	9.84
5	6.91