



Telephone: 847.549.7600  
 800.323.4340  
 Fax: 847.247.2929  
 E-mail: [techinfo@coleparmer.com](mailto:techinfo@coleparmer.com)  
 Web: [www.coleparmer.com](http://www.coleparmer.com)

**032-15-GL      FLOWMETER CALIBRATION DATA      032/72**

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		0787-A1-AM-04N

Max. Flow	Min. Flow	Units	Metering Fluid	Date
46.0	2.00	std. ml/min	oxygen	30-Nov-1999

<b>Model Number</b>		<b>Metering Temperature</b>	70.0 °F
<b>Tube Number</b>	032-15-GL	<b>Metering Pressure</b>	14.70 psia
<b>Serial Number</b>		<b>Metering density</b>	0.001326 g/ml
<b>Float Material</b>	glass	<b>Metering Viscosity</b>	0.02030 cp
<b>Float Density</b>	2.53 g/ml	<b>Density at STD.Cond</b>	0.001326 g/ml
<b>STD. Conditions</b>	STP: 1 atm @ 70 °	<b>Accuracy</b>	std.
<b>Room Temperature</b>	70.0 °F	<b>Barometric Pressure</b>	14.70 psia

SCALE READINGS AT CENTER OF FLOAT	
Scale Reading (mm)	Flow
65	46.0
60	40.3
55	35.0
50	29.8
45	25.0
40	20.7
35	16.8
30	13.5
25	10.6
20	8.00
15	5.80
10	4.00
5	2.00