

032-15-GL

FLOWMETER CALIBRATION DATA

032/13

CUSTOMER	CUST. P.O. No	REF. CURVE NUMBER
		0787-A1-AM-04N

Max. Flow	Min. Flow	Units	Metering Fluid	Date
0.550	0.009	std. ml/min	water	30-Nov-1999

Model Number	03216-04	Metering Temperature	70.0 °F
Tube Number	032-15-GL	Metering Pressure	14.70 psia
Serial Number		Metering density	1.000 g/ml
Float Material	glass	Metering Viscosity	1.000 cp
Float Density	2.53 g/ml	Density at STD.Cond	1.000 g/ml
STD. Conditions	STP: 1 atm @ 70 °	Accuracy	Standard
Room Temperature	70.0 °F	Barometric Pressure	14.70 psia

SCALE READINGS AT CENTER OF FLOAT	
Scale Reading (mm)	Flow
65	0.550
60	0.490
55	0.430
50	0.370
45	0.320
40	0.270
35	0.220
30	0.170
25	0.130
20	0.095
15	0.060
10	0.035
5	0.009