

# AMTS series cleanroom tables

Pharma stainless steel tables suitable for cleanrooms



AMTS-90x75

Type	Performance	Surface	Isolation	Application
AMTS-75x75	Scientific	Stainless	Damped sorbothane	Cleanrooms
AMTS-90x75	Scientific	Stainless	Damped sorbothane	Cleanrooms
AMTS-120x75	Scientific	Stainless	Damped sorbothane	Cleanrooms

- A range of pharma stainless worktop tables suitable for use in cleanrooms
- Welded box section white powder epoxy coated frames are easy to clean and stainless frames are optional
- Wide range of accessories creates the best environment, increasing performance, productivity and user comfort
- Satin silicon stainless is suitable for cleanrooms with a 0.25 Ra finish and a seamless stainless frame is optional
- Available in 750 and 900mm working heights.

The seamless design and pharma grade satin silicon finished stainless steel worktop featured in the AMTS series makes these tables ideal for use in cleanrooms and in Medical and Biological environments. Frames have adjustable levelling feet and are suitable for loads up to 200kgs. 316 stainless versions are available for more demanding applications



AMTR-120x75-900 trespa top




Option F02 frame shelf



Option F27 keyboard shelf

## Dimensions mm's



## Specifications AMTS series tables

Worktop dimensions (LxW)mm's	750x750;900x750;1200x750	AMTS-LxW table
Working height mm's	750 (900 on request)	Options:
Load capacity	200kgs	F02 Frame shelf
Level adjustment (mm's;ins)	+/-15	F06 Foot castors
Surfaces	Top pharma grade stainless steel Frame powder white epoxy	F05 Guard rails
Working temperature	-20 to +160 deg C	F07 Bracket set
Bacterial resistance	No growth	F08 Arm rest bar
Fungal resistance	No growth	F10 LCD monitor post
Heat aging	Stable	F15 Gel arm rests
Shipping weight	50kgs in 2 boxes (flatpacked top and frame)	F27 Keyboard shelf

Note: Options F05,F08 &F10 require Option F07 to function